

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770836

Luminaire Tested: LD6D70BD010-EU6DR6570959027-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770836
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR6570959027-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7226.7 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770836
CATALOG NUMBER: LD6D70BD010-EU6DR6570959027-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P770836

CATALOG NUMBER: LD6D70BD010-EU6DR6570959027-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	383223
5°	382260
10°	381929
15°	370155
20°	336982
25°	293660
30°	244244
35°	193524
40°	139673
45°	88245
50°	45993
55°	24448
60°	12837
65°	7062
70°	2971
75°	3272
80°	2253
85°	1943

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 88245 cd/sqm



TEST NUMBER: P770836

CATALOG NUMBER: LD6D70BD010-EU6DR6570959027-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	620.5	8.6
10°-20°	1699.2	23.5
20°-30°	2077.0	28.7
30°-40°	1685.2	23.3
40°-50°	839.8	11.6
50°-60°	234.2	3.2
60°-70°	53.2	0.7
70°-80°	13.9	0.2
80°-90°	3.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4396.8	60.8
0°-40°	6082.0	84.2
0°-60°	7156.1	99.0
0°-90°	7226.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7226.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6562	
5°	6520	621
15°	6122	1699
25°	4557	2077
35°	2714	1685
45°	1068	840
55°	240	234
65°	51	53
75°	14	14
85°	3	4
90°	0	



TEST NUMBER: P770836

CATALOG NUMBER: LD6D70BD010-EU6DR6570959027-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	6561.6
2.5°	6556.8
5°	6520.2
7.5°	6499.0
10°	6440.1
12.5°	6320.6
15°	6121.9
17.5°	5811.5
20°	5421.9
22.5°	5001.5
25°	4557.0
27.5°	4081.6
30°	3621.7
32.5°	3167.5
35°	2714.3
37.5°	2262.1
40°	1832.0
42.5°	1429.0
45°	1068.4
47.5°	744.4
50°	506.2
52.5°	349.1
55°	240.1
57.5°	162.0
60°	109.9
62.5°	76.2
65°	51.1
67.5°	26.0
70°	17.4
72.5°	16.4
75°	14.5
77.5°	9.6
80°	6.7
82.5°	4.8
85°	2.9
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)