

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770849

Luminaire Tested: LD6D70BD010-EU6DR6570959030-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770849
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR6570959030-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7445.1 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770849
CATALOG NUMBER: LD6D70BD010-EU6DR6570959030-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P770849

CATALOG NUMBER: LD6D70BD010-EU6DR6570959030-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	394804
5°	393809
10°	393476
15°	381341
20°	347169
25°	302534
30°	251622
35°	199378
40°	143897
45°	90913
50°	47384
55°	25191
60°	13223
65°	7269
70°	3057
75°	3362
80°	2354
85°	2010

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 90913 cd/sqm



TEST NUMBER: P770849

CATALOG NUMBER: LD6D70BD010-EU6DR6570959030-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	639.3	8.6
10°-20°	1750.6	23.5
20°-30°	2139.8	28.7
30°-40°	1736.2	23.3
40°-50°	865.2	11.6
50°-60°	241.3	3.2
60°-70°	54.8	0.7
70°-80°	14.3	0.2
80°-90°	3.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4529.7	60.8
0°-40°	6265.8	84.2
0°-60°	7372.3	99.0
0°-90°	7445.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7445.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6760	
5°	6717	639
15°	6307	1751
25°	4695	2140
35°	2796	1736
45°	1101	865
55°	247	241
65°	53	55
75°	15	14
85°	3	4
90°	0	



TEST NUMBER: P770849

CATALOG NUMBER: LD6D70BD010-EU6DR6570959030-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	6759.9
2.5°	6755.0
5°	6717.2
7.5°	6695.4
10°	6634.8
12.5°	6511.6
15°	6306.9
17.5°	5987.1
20°	5585.8
22.5°	5152.6
25°	4694.7
27.5°	4205.0
30°	3731.1
32.5°	3263.2
35°	2796.4
37.5°	2330.5
40°	1887.4
42.5°	1472.2
45°	1100.7
47.5°	766.9
50°	521.5
52.5°	359.6
55°	247.4
57.5°	166.9
60°	113.2
62.5°	78.5
65°	52.6
67.5°	26.8
70°	17.9
72.5°	16.9
75°	14.9
77.5°	9.9
80°	7.0
82.5°	5.0
85°	3.0
87.5°	2.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)