

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770342

Luminaire Tested: LD6D70BD010-EU6DR3070959050-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770342
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR3070959050-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8839.2 lumens
Efficiency: N/A
Efficacy: 132.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P770342
CATALOG NUMBER: LD6D70BD010-EU6DR3070959050-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P770342

CATALOG NUMBER: LD6D70BD010-EU6DR3070959050-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2175547	2175547	2175547
5°	2113091	2110625	2113199
10°	1830257	1817347	1829822
15°	1194153	1187734	1181767
20°	593796	616075	592998
25°	299110	337302	292987
30°	119761	130491	104338
35°	55551	53197	44591
40°	23981	26629	22592
45°	16919	21000	17071
50°	5811	15290	6145
55°	3350	6325	3536
60°	2342	2771	2342
65°	1521	1521	1521
70°	940	627	940
75°	0	414	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 21000 cd/sqm



TEST NUMBER: P770342

CATALOG NUMBER: LD6D70BD010-EU6DR3070959050-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2499.3	28.3
10°-20°	4025.2	45.5
20°-30°	1739.4	19.7
30°-40°	396.4	4.5
40°-50°	136.1	1.5
50°-60°	33.2	0.4
60°-70°	8.6	0.1
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8263.9	93.5
0°-40°	8660.3	98.0
0°-60°	8829.7	99.9
0°-90°	8839.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8839.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	28422	28422	28422	28422	28422	
5°	27501	27475	27469	27526	27503	2501
15°	15069	14888	14988	14940	14913	4035
25°	3542	3676	3994	3582	3469	1695
35°	594	607	569	565	477	403
45°	156	194	194	194	158	111
55°	25	26	47	28	26	24
65°	8	8	8	8	8	8
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P770342

CATALOG NUMBER: LD6D70BD010-EU6DR3070959050-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	28422.4	28422.4	28422.4	28422.4	28422.4
2.5°	28234.0	28214.4	28225.6	28239.6	28245.1
5°	27501.4	27474.9	27469.3	27526.5	27502.8
7.5°	26023.6	25985.9	25928.7	26058.5	26179.9
10°	23548.1	23506.2	23382.0	23443.4	23542.5
12.5°	19893.4	19758.1	19755.3	19950.6	19924.1
15°	15069.4	14888.0	14988.4	14939.6	14913.1
17.5°	10133.7	10063.9	10197.9	10157.4	9983.0
20°	7289.8	7307.9	7563.3	7434.9	7280.0
22.5°	5319.4	5385.0	5687.8	5357.1	5235.7
25°	3541.6	3675.6	3993.8	3582.1	3469.1
27.5°	2178.3	2239.7	2562.0	2150.4	2089.0
30°	1355.0	1324.3	1476.4	1267.1	1180.5
32.5°	888.9	849.8	898.7	806.6	736.8
35°	594.5	607.0	569.3	565.2	477.2
37.5°	371.2	427.0	376.8	401.9	307.0
40°	240.0	309.8	266.5	294.4	226.1
42.5°	196.8	238.6	219.1	233.0	200.9
45°	156.3	194.0	194.0	194.0	157.7
47.5°	86.5	129.8	166.1	132.6	92.1
50°	48.8	65.6	128.4	68.4	51.6
52.5°	33.5	37.7	87.9	39.1	34.9
55°	25.1	26.5	47.4	27.9	26.5
57.5°	19.5	20.9	25.1	20.9	19.5
60°	15.3	15.3	18.1	16.7	15.3
62.5°	11.2	11.2	12.6	11.2	11.2
65°	8.4	8.4	8.4	8.4	8.4
67.5°	4.2	5.6	5.6	5.6	5.6
70°	4.2	2.8	2.8	2.8	4.2
72.5°	2.8	1.4	1.4	1.4	1.4
75°	0.0	0.0	1.4	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)