

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771629

Luminaire Tested: LD6D75BD010-EU6DR6570959030-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P771629
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6570959030-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7868.8 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P771629
CATALOG NUMBER: LD6D75BD010-EU6DR6570959030-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P771629

CATALOG NUMBER: LD6D75BD010-EU6DR6570959030-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	417284
5°	416228
10°	415875
15°	403054
20°	366934
25°	319759
30°	265946
35°	210728
40°	152093
45°	96083
50°	50082
55°	26617
60°	13982
65°	7684
70°	3227
75°	3543
80°	2455
85°	2077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 96083 cd/sqm



TEST NUMBER: P771629

CATALOG NUMBER: LD6D75BD010-EU6DR6570959030-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	675.7	8.6
10°-20°	1850.2	23.5
20°-30°	2261.6	28.7
30°-40°	1835.0	23.3
40°-50°	914.4	11.6
50°-60°	255.1	3.2
60°-70°	57.9	0.7
70°-80°	15.1	0.2
80°-90°	3.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4787.5	60.8
0°-40°	6622.6	84.2
0°-60°	7792.0	99.0
0°-90°	7868.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7868.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7145	
5°	7100	676
15°	6666	1850
25°	4962	2262
35°	2956	1835
45°	1163	914
55°	261	255
65°	56	58
75°	16	15
85°	3	4
90°	0	



TEST NUMBER: P771629

CATALOG NUMBER: LD6D75BD010-EU6DR6570959030-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7144.8
2.5°	7139.5
5°	7099.6
7.5°	7076.5
10°	7012.5
12.5°	6882.3
15°	6666.0
17.5°	6327.9
20°	5903.8
22.5°	5446.0
25°	4962.0
27.5°	4444.4
30°	3943.5
32.5°	3449.0
35°	2955.6
37.5°	2463.1
40°	1994.9
42.5°	1556.0
45°	1163.3
47.5°	810.5
50°	551.2
52.5°	380.1
55°	261.4
57.5°	176.4
60°	119.7
62.5°	82.9
65°	55.6
67.5°	28.3
70°	18.9
72.5°	17.8
75°	15.7
77.5°	10.5
80°	7.3
82.5°	5.2
85°	3.1
87.5°	2.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)