

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771017

Luminaire Tested: LD6D75BD010-EU6DR2570959035-6LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771017  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR2570959035-6LBS1B  
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 25° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7591.1 lumens  
Efficiency: N/A  
Efficacy: 104.8 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P771017  
CATALOG NUMBER: LD6D75BD010-EU6DR2570959035-6LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P771017

CATALOG NUMBER: LD6D75BD010-EU6DR2570959035-6LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3145770
5°	2929886
10°	2089962
15°	1230907
20°	765889
25°	420318
30°	192223
35°	72800
40°	32962
45°	19825
50°	8227
55°	5296
60°	3693
65°	2508
70°	383
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19825 cd/sqm



TEST NUMBER: P771017

CATALOG NUMBER: LD6D75BD010-EU6DR2570959035-6LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2295.8	30.2
10°-20°	3109.5	41.0
20°-30°	1645.5	21.7
30°-40°	406.2	5.4
40°-50°	99.1	1.3
50°-60°	26.1	0.3
60°-70°	8.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7050.8	92.9
0°-40°	7457.0	98.2
0°-60°	7582.2	99.9
0°-90°	7591.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7591.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	28791	
5°	26714	###
15°	10882	3110
25°	3486	1645
35°	546	406
45°	128	99
55°	28	26
65°	10	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P771017

CATALOG NUMBER: LD6D75BD010-EU6DR2570959035-6LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	28791.4
2.5°	28318.2
5°	26713.5
7.5°	23489.6
10°	18837.6
12.5°	14240.2
15°	10881.9
17.5°	8480.9
20°	6587.0
22.5°	4939.9
25°	3486.5
27.5°	2338.1
30°	1523.6
32.5°	927.0
35°	545.8
37.5°	334.0
40°	231.1
42.5°	176.7
45°	128.3
47.5°	77.5
50°	48.4
52.5°	35.1
55°	27.8
57.5°	21.8
60°	16.9
62.5°	13.3
65°	9.7
67.5°	3.6
70°	1.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)