

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P759644

Luminaire Tested: LD6D08D010-EU6DR600210IC9030-6LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P759644  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D08D010-EU6DR600210IC9030-6LBDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 613.9 lumens  
Efficiency: N/A  
Efficacy: 69.0 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P759644

CATALOG NUMBER: LD6D08D010-EU6DR600210IC9030-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P759644

CATALOG NUMBER: LD6D08D010-EU6DR600210IC9030-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53			53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	79662
5°	81622
10°	82611
15°	78694
20°	69392
25°	56119
30°	37963
35°	19020
40°	3095
45°	3013
50°	3077
55°	3124
60°	3212
65°	3283
70°	3354
75°	3419
80°	3272
85°	2758

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 3419 cd/sqm



TEST NUMBER: P759644

CATALOG NUMBER: LD6D08D010-EU6DR600210IC9030-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	71.1	11.6
10°-20°	192.5	31.3
20°-30°	207.1	33.7
30°-40°	90.0	14.7
40°-50°	15.1	2.5
50°-60°	14.7	2.4
60°-70°	12.6	2.0
70°-80°	8.4	1.4
80°-90°	2.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	470.6	76.7
0°-40°	560.6	91.3
0°-60°	590.4	96.2
0°-90°	613.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	613.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	729	
5°	744	71
15°	696	192
25°	466	207
35°	143	90
45°	20	15
55°	16	15
65°	13	13
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P759644

CATALOG NUMBER: LD6D08D010-EU6DR600210IC9030-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	729.1
2.5°	749.6
5°	744.2
7.5°	745.9
10°	744.6
12.5°	729.3
15°	695.7
17.5°	650.8
20°	596.8
22.5°	539.0
25°	465.5
27.5°	372.4
30°	300.9
32.5°	231.9
35°	142.6
37.5°	61.0
40°	21.7
42.5°	19.9
45°	19.5
47.5°	18.9
50°	18.1
52.5°	17.2
55°	16.4
57.5°	15.6
60°	14.7
62.5°	13.8
65°	12.7
67.5°	11.7
70°	10.5
72.5°	9.3
75°	8.1
77.5°	6.6
80°	5.2
82.5°	3.7
85°	2.2
87.5°	0.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)