

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P758986

Luminaire Tested: LD6D08D010-EU6DR150210IC9050-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P758986  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D08D010-EU6DR150210IC9050-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 886.1 lumens  
Efficiency: N/A  
Efficacy: 99.6 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct

Input Watts (W): 8.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P758986  
CATALOG NUMBER: LD6D08D010-EU6DR150210IC9050-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P758986

CATALOG NUMBER: LD6D08D010-EU6DR150210IC9050-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1358386	1358386	1358386
5°	798254	787919	794149
10°	238242	239912	243579
15°	59262	60418	58550
20°	17731	20529	18107
25°	6248	7961	6333
30°	2299	3025	2336
35°	1147	1300	1111
40°	724	795	724
45°	539	574	539
50°	424	424	424
55°	355	355	355
60°	288	288	288
65°	221	221	221
70°	190	190	190
75°	113	113	151
80°	79	79	79
85°	42	42	42

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 574 cd/sqm



TEST NUMBER: P758986

CATALOG NUMBER: LD6D08D010-EU6DR150210IC9050-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	574.7	64.9
10°-20°	236.4	26.7
20°-30°	47.0	5.3
30°-40°	11.7	1.3
40°-50°	6.2	0.7
50°-60°	4.6	0.5
60°-70°	3.3	0.4
70°-80°	1.8	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	858.0	96.8
0°-40°	869.7	98.2
0°-60°	880.4	99.4
0°-90°	886.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	886.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	12072	12072	12072	12072	12072	
5°	7855	7774	7753	7806	7814	574
15°	682	695	696	683	674	234
25°	80	91	102	90	81	42
35°	16	17	18	17	15	11
45°	8	8	8	8	8	6
55°	5	5	5	5	5	5
65°	3	3	3	3	3	3
75°	2	2	2	2	2	2
85°	0	0	0	0	0	1
90°	0	0	0	0	0	



TEST NUMBER: P758986

CATALOG NUMBER: LD6D08D010-EU6DR150210IC9050-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	12072.4	12072.4	12072.4	12072.4	12072.4
2.5°	10889.8	10899.0	10902.6	10913.3	10953.2
5°	7854.6	7773.8	7752.9	7806.5	7814.2
7.5°	4652.7	4669.1	4728.9	4742.2	4694.1
10°	2553.3	2574.2	2571.2	2589.6	2610.5
12.5°	1305.8	1289.4	1284.3	1305.3	1276.1
15°	682.3	695.1	695.6	683.3	674.1
17.5°	366.9	381.8	406.3	386.4	355.7
20°	216.7	230.0	250.9	234.6	221.3
22.5°	133.9	144.6	159.5	146.7	135.9
25°	80.2	91.0	102.2	90.5	81.3
27.5°	47.5	56.7	63.9	56.2	47.0
30°	30.7	35.8	40.4	35.3	31.2
32.5°	21.5	23.5	25.6	23.5	21.5
35°	15.8	16.9	17.9	16.9	15.3
37.5°	12.3	13.3	13.8	12.8	11.8
40°	10.2	10.7	11.2	10.7	10.2
42.5°	8.7	9.2	9.2	9.2	8.7
45°	7.7	7.7	8.2	7.7	7.7
47.5°	6.6	6.6	7.2	6.6	6.6
50°	6.1	6.1	6.1	6.1	6.1
52.5°	5.6	5.6	5.6	5.6	5.6
55°	5.1	5.1	5.1	5.1	5.1
57.5°	4.6	4.6	4.6	4.6	4.6
60°	4.1	4.1	4.1	4.1	4.1
62.5°	3.6	3.6	3.6	3.6	3.6
65°	3.1	3.1	3.1	3.1	3.1
67.5°	3.1	3.1	3.1	3.1	3.1
70°	2.6	2.6	2.6	2.6	2.6
72.5°	2.0	2.0	2.0	2.0	2.0
75°	1.5	1.5	1.5	1.5	2.0
77.5°	1.5	1.5	1.5	1.5	1.5
80°	1.0	1.0	1.0	1.0	1.0
82.5°	1.0	1.0	1.0	1.0	1.0
85°	0.5	0.5	0.5	0.5	0.5
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)