

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773093

Luminaire Tested: LD6D85BD010-EU6DR6070959027-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773093
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR6070959027-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7887.3 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P773093
CATALOG NUMBER: LD6D85BD010-EU6DR6070959027-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P773093

CATALOG NUMBER: LD6D85BD010-EU6DR6070959027-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80		
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70		
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62		
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1023467
5°	1048632
10°	1061301
15°	1011034
20°	891418
25°	720997
30°	487697
35°	244384
40°	39637
45°	38799
50°	39571
55°	40174
60°	41301
65°	42244
70°	43223
75°	43735
80°	42157
85°	35102

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 43735 cd/sqm



TEST NUMBER: P773093

CATALOG NUMBER: LD6D85BD010-EU6DR6070959027-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	913.8	11.6
10°-20°	2472.3	31.3
20°-30°	2660.0	33.7
30°-40°	1156.2	14.7
40°-50°	194.2	2.5
50°-60°	188.8	2.4
60°-70°	161.5	2.0
70°-80°	108.1	1.4
80°-90°	32.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6046.1	76.7
0°-40°	7202.4	91.3
0°-60°	7585.4	96.2
0°-90°	7887.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7887.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9367	
5°	9561	914
15°	8938	2472
25°	5981	2660
35°	1832	1156
45°	251	194
55°	211	189
65°	163	162
75°	104	108
85°	28	32
90°	0	



TEST NUMBER: P773093

CATALOG NUMBER: LD6D85BD010-EU6DR6070959027-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	9367.2
2.5°	9630.5
5°	9561.0
7.5°	9582.9
10°	9565.9
12.5°	9368.4
15°	8938.1
17.5°	8360.2
20°	7666.6
22.5°	6924.2
25°	5980.6
27.5°	4783.5
30°	3865.6
32.5°	2979.4
35°	1832.2
37.5°	783.8
40°	277.9
42.5°	256.0
45°	251.1
47.5°	242.6
50°	232.8
52.5°	221.9
55°	210.9
57.5°	199.9
60°	189.0
62.5°	176.8
65°	163.4
67.5°	149.9
70°	135.3
72.5°	119.5
75°	103.6
77.5°	85.3
80°	67.0
82.5°	47.5
85°	28.0
87.5°	9.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)