

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773251

Luminaire Tested: LD6D85BD010-EU6DR7070959027-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773251
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR7070959027-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10585.7 lumens
Efficiency: N/A
Efficacy: 120.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P773251
CATALOG NUMBER: LD6D85BD010-EU6DR7070959027-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P773251

CATALOG NUMBER: LD6D85BD010-EU6DR7070959027-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65		
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50		
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1300356
5°	1261715
10°	1226544
15°	1210456
20°	1130312
25°	849148
30°	600273
35°	212625
40°	111807
45°	119087
50°	123320
55°	125628
60°	126415
65°	123734
70°	116794
75°	108197
80°	96017
85°	77976

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 126444 cd/sqm



TEST NUMBER: P773251

CATALOG NUMBER: LD6D85BD010-EU6DR7070959027-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1085.1	10.3
10°-20°	2976.3	28.1
20°-30°	3277.9	31.0
30°-40°	1252.4	11.8
40°-50°	591.4	5.6
50°-60°	587.9	5.6
60°-70°	470.7	4.4
70°-80°	270.5	2.6
80°-90°	73.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7339.2	69.3
0°-40°	8591.6	81.2
0°-60°	9770.9	92.3
0°-90°	10585.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10585.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11901	
5°	11504	###
15°	10701	2976
25°	7044	3278
35°	1594	1252
45°	771	591
55°	660	588
65°	479	471
75°	256	271
85°	62	74
90°	0	



TEST NUMBER: P773251

CATALOG NUMBER: LD6D85BD010-EU6DR7070959027-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	11901.4
2.5°	11777.0
5°	11503.8
7.5°	11275.8
10°	11055.3
12.5°	10868.8
15°	10701.1
17.5°	10295.9
20°	9721.2
22.5°	8481.3
25°	7043.6
27.5°	6131.6
30°	4757.9
32.5°	3073.3
35°	1594.1
37.5°	861.1
40°	783.9
42.5°	778.2
45°	770.7
47.5°	753.7
50°	725.5
52.5°	693.4
55°	659.5
57.5°	621.8
60°	578.5
62.5°	529.5
65°	478.6
67.5°	422.1
70°	365.6
72.5°	309.0
75°	256.3
77.5°	201.6
80°	152.6
82.5°	107.4
85°	62.2
87.5°	24.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)