

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773279

Luminaire Tested: LD6D85BD010-EU6DR7070959035-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773279
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR7070959035-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10283.7 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P773279

CATALOG NUMBER: LD6D85BD010-EU6DR7070959035-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P773279

CATALOG NUMBER: LD6D85BD010-EU6DR7070959035-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91	89	87	85
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85	82	79	78
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79	76	73	71
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74	70	67	65
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69	65	62	60
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65	61	57	56
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61	56	53	51
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57	53	49	48
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54	49	46	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	886848
5°	884631
10°	882722
15°	882478
20°	873849
25°	820865
30°	731798
35°	583470
40°	387425
45°	231623
50°	120074
55°	63109
60°	22333
65°	388
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 231623 cd/sqm



TEST NUMBER: P773279

CATALOG NUMBER: LD6D85BD010-EU6DR7070959035-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	767.0	7.5
10°-20°	2199.9	21.4
20°-30°	3103.4	30.2
30°-40°	2679.1	26.1
40°-50°	1199.7	11.7
50°-60°	314.1	3.1
60°-70°	20.5	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6070.4	59.0
0°-40°	8749.4	85.1
0°-60°	10263.3	99.8
0°-90°	10283.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10283.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8117	
5°	8066	767
15°	7802	2200
25°	6809	3103
35°	4374	2679
45°	1499	1200
55°	331	314
65°	2	20
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P773279

CATALOG NUMBER: LD6D85BD010-EU6DR7070959035-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	8116.8
2.5°	8108.1
5°	8065.7
7.5°	8030.7
10°	7956.3
12.5°	7889.1
15°	7801.6
17.5°	7700.8
20°	7515.5
22.5°	7210.4
25°	6809.0
27.5°	6343.4
30°	5800.4
32.5°	5136.3
35°	4374.4
37.5°	3533.7
40°	2716.3
42.5°	2063.9
45°	1499.0
47.5°	1033.4
50°	706.4
52.5°	487.5
55°	331.3
57.5°	200.0
60°	102.2
62.5°	32.1
65°	1.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)