

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773940

Luminaire Tested: LD6D90BD010-EU6DR6570959024-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773940
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR6570959024-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8605.8 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P773940

CATALOG NUMBER: LD6D90BD010-EU6DR6570959024-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P773940

CATALOG NUMBER: LD6D90BD010-EU6DR6570959024-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	925766
5°	926528
10°	959153
15°	960743
20°	884523
25°	753655
30°	576945
35°	407604
40°	240602
45°	97671
50°	35407
55°	19716
60°	11319
65°	6231
70°	6549
75°	5066
80°	5285
85°	4513

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 97671 cd/sqm



TEST NUMBER: P773940

CATALOG NUMBER: LD6D90BD010-EU6DR6570959024-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	815.9	9.5
10°-20°	2353.4	27.3
20°-30°	2823.7	32.8
30°-40°	1897.6	22.1
40°-50°	568.0	6.6
50°-60°	100.3	1.2
60°-70°	28.5	0.3
70°-80°	14.0	0.2
80°-90°	4.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5993.0	69.6
0°-40°	7890.6	91.7
0°-60°	8558.9	99.5
0°-90°	8605.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8605.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8473	
5°	8448	816
15°	8494	2353
25°	6252	2824
35°	3056	1898
45°	632	568
55°	104	100
65°	24	29
75°	12	14
85°	4	4
90°	0	



TEST NUMBER: P773940

CATALOG NUMBER: LD6D90BD010-EU6DR6570959024-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	8473.0
2.5°	8509.1
5°	8447.7
7.5°	8575.4
10°	8645.2
12.5°	8628.3
15°	8493.5
17.5°	8163.6
20°	7607.3
22.5°	6952.3
25°	6251.5
27.5°	5460.4
30°	4573.0
32.5°	3768.7
35°	3055.9
37.5°	2351.5
40°	1686.9
42.5°	1101.7
45°	632.1
47.5°	334.7
50°	208.3
52.5°	144.5
55°	103.5
57.5°	74.7
60°	51.8
62.5°	33.7
65°	24.1
67.5°	21.7
70°	20.5
72.5°	15.7
75°	12.0
77.5°	10.8
80°	8.4
82.5°	6.0
85°	3.6
87.5°	2.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)