

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773957

Luminaire Tested: LD6D90BD010-EU6DR6570959027-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR6570959027-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10261.5 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P773957

CATALOG NUMBER: LD6D90BD010-EU6DR6570959027-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P773957

CATALOG NUMBER: LD6D90BD010-EU6DR6570959027-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	544161
5°	542786
10°	542325
15°	525609
20°	478503
25°	416982
30°	346812
35°	274797
40°	198333
45°	125297
50°	65310
55°	34712
60°	18234
65°	10033
70°	4201
75°	4626
80°	3229
85°	2747

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 125297 cd/sqm



TEST NUMBER: P773957

CATALOG NUMBER: LD6D90BD010-EU6DR6570959027-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	881.1	8.6
10°-20°	2412.8	23.5
20°-30°	2949.3	28.7
30°-40°	2393.0	23.3
40°-50°	1192.4	11.6
50°-60°	332.6	3.2
60°-70°	75.6	0.7
70°-80°	19.7	0.2
80°-90°	5.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6243.2	60.8
0°-40°	8636.2	84.2
0°-60°	10161.2	99.0
0°-90°	10261.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10261.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9317	
5°	9258	881
15°	8693	2413
25°	6471	2949
35°	3854	2393
45°	1517	1192
55°	341	333
65°	73	76
75°	20	20
85°	4	5
90°	0	



TEST NUMBER: P773957
CATALOG NUMBER: LD6D90BD010-EU6DR6570959027-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9317.2
2.5°	9310.4
5°	9258.3
7.5°	9228.2
10°	9144.7
12.5°	8974.9
15°	8692.9
17.5°	8252.0
20°	7698.9
22.5°	7101.9
25°	6470.7
27.5°	5795.7
30°	5142.6
32.5°	4497.7
35°	3854.2
37.5°	3212.1
40°	2601.4
42.5°	2029.1
45°	1517.0
47.5°	1057.0
50°	718.8
52.5°	495.6
55°	340.9
57.5°	230.0
60°	156.1
62.5°	108.2
65°	72.6
67.5°	37.0
70°	24.6
72.5°	23.3
75°	20.5
77.5°	13.7
80°	9.6
82.5°	6.8
85°	4.1
87.5°	2.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)