

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773540

Luminaire Tested: LD6D90BD010-EU6DR3570959050-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P773540  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D90BD010-EU6DR3570959050-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11692.1 lumens  
Efficiency: N/A  
Efficacy: 118.2 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 98.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P773540

CATALOG NUMBER: LD6D90BD010-EU6DR3570959050-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P773540

CATALOG NUMBER: LD6D90BD010-EU6DR3570959050-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3514962
5°	3432377
10°	3093482
15°	2401037
20°	1361834
25°	529819
30°	197660
35°	108347
40°	70816
45°	43095
50°	27435
55°	19392
60°	14182
65°	7704
70°	575
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 43095 cd/sqm



TEST NUMBER: P773540

CATALOG NUMBER: LD6D90BD010-EU6DR3570959050-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	2878.2	24.6
10°-20°	5619.5	48.1
20°-30°	2291.9	19.6
30°-40°	548.5	4.7
40°-50°	228.6	2.0
50°-60°	94.6	0.8
60°-70°	29.6	0.3
70°-80°	0.7	0.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	10789.6	92.3
0°-40°	11338.1	97.0
0°-60°	11661.3	99.7
0°-90°	11692.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11692.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	32170	
5°	31295	###
15°	21226	5620
25°	4395	2292
35°	812	548
45°	279	229
55°	102	95
65°	30	30
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P773540

CATALOG NUMBER: LD6D90BD010-EU6DR3570959050-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	32170.4
2.5°	31977.4
5°	31295.0
7.5°	29933.6
10°	27882.7
12.5°	24994.9
15°	21226.5
17.5°	16617.7
20°	11712.4
22.5°	7468.5
25°	4394.8
27.5°	2484.2
30°	1566.7
32.5°	1100.0
35°	812.3
37.5°	628.1
40°	496.5
42.5°	382.5
45°	278.9
47.5°	208.8
50°	161.4
52.5°	128.1
55°	101.8
57.5°	82.5
60°	64.9
62.5°	47.4
65°	29.8
67.5°	10.5
70°	1.8
72.5°	1.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)