

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760783

Luminaire Tested: LD6D10D010-EU6DR650210IC9050-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P760783
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR650210IC9050-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 747.1 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760783
CATALOG NUMBER: LD6D10D010-EU6DR650210IC9050-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P760783

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9050-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80372
5°	80438
10°	83276
15°	83411
20°	76787
25°	65438
30°	50087
35°	35386
40°	20881
45°	8483
50°	3077
55°	1714
60°	983
65°	543
70°	575
75°	422
80°	440
85°	376

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8483 cd/sqm



TEST NUMBER: P760783

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9050-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.8	9.5
10°-20°	204.3	27.3
20°-30°	245.2	32.8
30°-40°	164.7	22.0
40°-50°	49.3	6.6
50°-60°	8.7	1.2
60°-70°	2.5	0.3
70°-80°	1.2	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.3	69.6
0°-40°	685.0	91.7
0°-60°	743.0	99.5
0°-90°	747.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	747.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	736	
5°	733	71
15°	737	204
25°	543	245
35°	265	165
45°	55	49
55°	9	9
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P760783

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9050-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	735.6
2.5°	738.8
5°	733.4
7.5°	744.5
10°	750.6
12.5°	749.1
15°	737.4
17.5°	708.7
20°	660.4
22.5°	603.6
25°	542.8
27.5°	474.1
30°	397.0
32.5°	327.2
35°	265.3
37.5°	204.1
40°	146.4
42.5°	95.6
45°	54.9
47.5°	29.0
50°	18.1
52.5°	12.5
55°	9.0
57.5°	6.5
60°	4.5
62.5°	2.9
65°	2.1
67.5°	1.9
70°	1.8
72.5°	1.4
75°	1.0
77.5°	0.9
80°	0.7
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)