

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763118

Luminaire Tested: LD6D25D010-EU6DR3020359027-6LBSQW1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P763118  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D25D010-EU6DR3020359027-6LBSQW1MW  
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2254.6 lumens  
Efficiency: N/A  
Efficacy: 89.8 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P763118

CATALOG NUMBER: LD6D25D010-EU6DR3020359027-6LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P763118

CATALOG NUMBER: LD6D25D010-EU6DR3020359027-6LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	554909	554909	554909
5°	538980	538350	539003
10°	466843	463547	466726
15°	304588	302956	301427
20°	151459	157136	151255
25°	76298	86027	74735
30°	30546	33286	26613
35°	14166	13568	11381
40°	6115	6795	5755
45°	4319	5358	4352
50°	1477	3906	1572
55°	854	1615	907
60°	597	704	597
65°	380	380	380
70°	246	157	246
75°	0	89	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 5358 cd/sqm



TEST NUMBER: P763118

CATALOG NUMBER: LD6D25D010-EU6DR3020359027-6LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	637.5	28.3
10°-20°	1026.7	45.5
20°-30°	443.7	19.7
30°-40°	101.1	4.5
40°-50°	34.7	1.5
50°-60°	8.5	0.4
60°-70°	2.2	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2107.8	93.5
0°-40°	2209.0	98.0
0°-60°	2252.1	99.9
0°-90°	2254.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2254.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	7250	7250	7250	7250	7250	
5°	7015	7008	7006	7021	7015	638
15°	3844	3798	3823	3811	3804	1029
25°	903	938	1019	914	885	432
35°	152	155	145	144	122	103
45°	40	50	50	50	40	28
55°	6	7	12	7	7	6
65°	2	2	2	2	2	2
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P763118

CATALOG NUMBER: LD6D25D010-EU6DR3020359027-6LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	7249.6	7249.6	7249.6	7249.6	7249.6
2.5°	7201.6	7196.6	7199.4	7203.0	7204.4
5°	7014.7	7007.9	7006.5	7021.1	7015.0
7.5°	6637.7	6628.2	6613.6	6646.7	6677.6
10°	6006.4	5995.6	5964.0	5979.7	6004.9
12.5°	5074.2	5039.6	5038.9	5088.8	5082.0
15°	3843.7	3797.5	3823.1	3810.6	3803.8
17.5°	2584.8	2567.0	2601.1	2590.8	2546.3
20°	1859.4	1864.0	1929.1	1896.4	1856.9
22.5°	1356.8	1373.5	1450.8	1366.4	1335.4
25°	903.4	937.5	1018.6	913.7	884.9
27.5°	555.6	571.3	653.5	548.5	532.8
30°	345.6	337.8	376.6	323.2	301.1
32.5°	226.7	216.7	229.2	205.7	187.9
35°	151.6	154.8	145.2	144.2	121.8
37.5°	94.7	108.9	96.1	102.5	78.3
40°	61.2	79.0	68.0	75.1	57.6
42.5°	50.2	60.8	55.9	59.4	51.3
45°	39.9	49.5	49.5	49.5	40.2
47.5°	22.1	33.1	42.3	33.8	23.5
50°	12.4	16.7	32.8	17.4	13.2
52.5°	8.5	9.6	22.4	10.0	8.9
55°	6.4	6.8	12.1	7.1	6.8
57.5°	5.0	5.3	6.4	5.3	5.0
60°	3.9	3.9	4.6	4.3	3.9
62.5°	2.9	2.9	3.2	2.9	2.9
65°	2.1	2.1	2.1	2.1	2.1
67.5°	1.1	1.4	1.4	1.4	1.4
70°	1.1	0.7	0.7	0.7	1.1
72.5°	0.7	0.3	0.3	0.3	0.3
75°	0.0	0.0	0.3	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)