

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P763693

Luminaire Tested: LD6D25D010-EU6DR6520359040-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P763693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D25D010-EU6DR6520359040-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2757.4 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P763693
CATALOG NUMBER: LD6D25D010-EU6DR6520359040-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P763693

CATALOG NUMBER: LD6D25D010-EU6DR6520359040-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146226
5°	145858
10°	145730
15°	141238
20°	128580
25°	112051
30°	93194
35°	73843
40°	53300
45°	33674
50°	17545
55°	9327
60°	4894
65°	2695
70°	1127
75°	1241
80°	874
85°	737

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 33674 cd/sqm



TEST NUMBER: P763693

CATALOG NUMBER: LD6D25D010-EU6DR6520359040-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.8	8.6
10°-20°	648.4	23.5
20°-30°	792.5	28.7
30°-40°	643.0	23.3
40°-50°	320.4	11.6
50°-60°	89.4	3.2
60°-70°	20.3	0.7
70°-80°	5.3	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1677.7	60.8
0°-40°	2320.7	84.2
0°-60°	2730.5	99.0
0°-90°	2757.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2757.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2504	
5°	2488	237
15°	2336	648
25°	1739	793
35°	1036	643
45°	408	320
55°	92	89
65°	20	20
75°	6	5
85°	1	1
90°	0	



TEST NUMBER: P763693

CATALOG NUMBER: LD6D25D010-EU6DR6520359040-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2503.7
2.5°	2501.8
5°	2487.9
7.5°	2479.8
10°	2457.3
12.5°	2411.7
15°	2335.9
17.5°	2217.4
20°	2068.8
22.5°	1908.4
25°	1738.8
27.5°	1557.4
30°	1381.9
32.5°	1208.6
35°	1035.7
37.5°	863.2
40°	699.1
42.5°	545.3
45°	407.7
47.5°	284.0
50°	193.1
52.5°	133.2
55°	91.6
57.5°	61.8
60°	41.9
62.5°	29.0
65°	19.5
67.5°	9.9
70°	6.6
72.5°	6.2
75°	5.5
77.5°	3.7
80°	2.6
82.5°	1.8
85°	1.1
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)