

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766930

Luminaire Tested: LD6D45BD010-EU6DR6540509027-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P766930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR6540509027-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4266.7 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P766930
CATALOG NUMBER: LD6D45BD010-EU6DR6540509027-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P766930

CATALOG NUMBER: LD6D45BD010-EU6DR6540509027-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	226262
5°	225690
10°	225495
15°	218548
20°	198955
25°	173380
30°	144205
35°	114262
40°	82470
45°	52101
50°	27158
55°	14439
60°	7581
65°	4173
70°	1742
75°	1918
80°	1345
85°	1139

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 52101 cd/sqm



TEST NUMBER: P766930

CATALOG NUMBER: LD6D45BD010-EU6DR6540509027-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.4	8.6
10°-20°	1003.2	23.5
20°-30°	1226.3	28.7
30°-40°	995.0	23.3
40°-50°	495.8	11.6
50°-60°	138.3	3.2
60°-70°	31.4	0.7
70°-80°	8.2	0.2
80°-90°	2.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2595.9	60.8
0°-40°	3590.9	84.2
0°-60°	4225.0	99.0
0°-90°	4266.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4266.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3874	
5°	3850	366
15°	3614	1003
25°	2690	1226
35°	1603	995
45°	631	496
55°	142	138
65°	30	31
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P766930

CATALOG NUMBER: LD6D45BD010-EU6DR6540509027-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3874.1
2.5°	3871.2
5°	3849.6
7.5°	3837.0
10°	3802.3
12.5°	3731.7
15°	3614.5
17.5°	3431.1
20°	3201.1
22.5°	2952.9
25°	2690.5
27.5°	2409.8
30°	2138.3
32.5°	1870.1
35°	1602.6
37.5°	1335.6
40°	1081.7
42.5°	843.7
45°	630.8
47.5°	439.5
50°	298.9
52.5°	206.1
55°	141.8
57.5°	95.6
60°	64.9
62.5°	45.0
65°	30.2
67.5°	15.4
70°	10.2
72.5°	9.7
75°	8.5
77.5°	5.7
80°	4.0
82.5°	2.8
85°	1.7
87.5°	1.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)