

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P766982

Luminaire Tested: LD6D45BD010-EU6DR6540509050-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P766982
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D45BD010-EU6DR6540509050-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4682.8 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P766982

CATALOG NUMBER: LD6D45BD010-EU6DR6540509050-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P766982
 CATALOG NUMBER: LD6D45BD010-EU6DR6540509050-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	248327
5°	247699
10°	247491
15°	239861
20°	218359
25°	190289
30°	158266
35°	125406
40°	90513
45°	57181
50°	29802
55°	15844
60°	8317
65°	4574
70°	1913
75°	2121
80°	1480
85°	1273

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 57181 cd/sqm



TEST NUMBER: P766982

CATALOG NUMBER: LD6D45BD010-EU6DR6540509050-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	402.1	8.6
10°-20°	1101.1	23.5
20°-30°	1345.9	28.7
30°-40°	1092.0	23.3
40°-50°	544.2	11.6
50°-60°	151.8	3.2
60°-70°	34.5	0.7
70°-80°	9.0	0.2
80°-90°	2.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2849.1	60.8
0°-40°	3941.1	84.2
0°-60°	4637.1	99.0
0°-90°	4682.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4682.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4252	
5°	4225	402
15°	3967	1101
25°	2953	1346
35°	1759	1092
45°	692	544
55°	156	152
65°	33	34
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P766982

CATALOG NUMBER: LD6D45BD010-EU6DR6540509050-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4251.9
2.5°	4248.8
5°	4225.0
7.5°	4211.3
10°	4173.2
12.5°	4095.7
15°	3967.0
17.5°	3765.8
20°	3513.3
22.5°	3240.9
25°	2952.9
27.5°	2644.8
30°	2346.8
32.5°	2052.5
35°	1758.9
37.5°	1465.8
40°	1187.2
42.5°	926.0
45°	692.3
47.5°	482.4
50°	328.0
52.5°	226.2
55°	155.6
57.5°	105.0
60°	71.2
62.5°	49.4
65°	33.1
67.5°	16.9
70°	11.2
72.5°	10.6
75°	9.4
77.5°	6.2
80°	4.4
82.5°	3.1
85°	1.9
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)