

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767710

Luminaire Tested: LD6D50D010-EU6DR6540509027-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P767710
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D50D010-EU6DR6540509027-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5010.8 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 47
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767710

CATALOG NUMBER: LD6D50D010-EU6DR6540509027-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P767710

CATALOG NUMBER: LD6D50D010-EU6DR6540509027-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	265720
5°	265053
10°	264826
15°	256658
20°	233655
25°	203616
30°	169353
35°	134190
40°	96849
45°	61187
50°	31892
55°	16954
60°	8901
65°	4892
70°	2049
75°	2257
80°	1581
85°	1340

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 61187 cd/sqm



TEST NUMBER: P767710

CATALOG NUMBER: LD6D50D010-EU6DR6540509027-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	430.3	8.6
10°-20°	1178.2	23.5
20°-30°	1440.2	28.7
30°-40°	1168.5	23.3
40°-50°	582.3	11.6
50°-60°	162.4	3.2
60°-70°	36.9	0.7
70°-80°	9.6	0.2
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3048.6	60.8
0°-40°	4217.2	84.2
0°-60°	4961.8	99.0
0°-90°	5010.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5010.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4550	
5°	4521	430
15°	4245	1178
25°	3160	1440
35°	1882	1169
45°	741	582
55°	166	162
65°	35	37
75°	10	10
85°	2	2
90°	0	



TEST NUMBER: P767710

CATALOG NUMBER: LD6D50D010-EU6DR6540509027-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4549.7
2.5°	4546.4
5°	4521.0
7.5°	4506.3
10°	4465.5
12.5°	4382.6
15°	4244.8
17.5°	4029.6
20°	3759.4
22.5°	3467.9
25°	3159.7
27.5°	2830.1
30°	2511.2
32.5°	2196.3
35°	1882.1
37.5°	1568.5
40°	1270.3
42.5°	990.8
45°	740.8
47.5°	516.1
50°	351.0
52.5°	242.0
55°	166.5
57.5°	112.3
60°	76.2
62.5°	52.8
65°	35.4
67.5°	18.1
70°	12.0
72.5°	11.4
75°	10.0
77.5°	6.7
80°	4.7
82.5°	3.3
85°	2.0
87.5°	1.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)