

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P767929

Luminaire Tested: LD6D55D010-EU6DR3055659024-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P767929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR3055659024-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4975.4 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')

CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P767929

CATALOG NUMBER: LD6D55D010-EU6DR3055659024-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P767929

CATALOG NUMBER: LD6D55D010-EU6DR3055659024-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1224557	1224557	1224557
5°	1189402	1188012	1189464
10°	1030203	1022936	1029962
15°	672160	668546	665186
20°	334229	346774	333781
25°	168364	189858	164909
30°	67411	73448	58732
35°	31266	29948	25099
40°	13499	14988	12710
45°	9526	11821	9612
50°	3275	8610	3465
55°	1882	3563	1988
60°	1317	1561	1317
65°	851	851	851
70°	537	358	537
75°	0	237	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 11821 cd/sqm



TEST NUMBER: P767929

CATALOG NUMBER: LD6D55D010-EU6DR3055659024-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1406.8	28.3
10°-20°	2265.7	45.5
20°-30°	979.1	19.7
30°-40°	223.1	4.5
40°-50°	76.6	1.5
50°-60°	18.7	0.4
60°-70°	4.8	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4651.5	93.5
0°-40°	4874.7	98.0
0°-60°	4970.0	99.9
0°-90°	4975.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4975.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	15998	15998	15998	15998	15998	
5°	15480	15465	15462	15494	15481	1408
15°	8482	8380	8437	8409	8394	2271
25°	1994	2069	2248	2016	1953	954
35°	335	342	320	318	269	227
45°	88	109	109	109	89	62
55°	14	15	27	16	15	14
65°	5	5	5	5	5	5
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P767929

CATALOG NUMBER: LD6D55D010-EU6DR3055659024-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	15998.2	15998.2	15998.2	15998.2	15998.2
2.5°	15892.2	15881.2	15887.5	15895.3	15898.4
5°	15479.8	15464.9	15461.7	15493.9	15480.6
7.5°	14648.0	14626.8	14594.6	14667.6	14736.0
10°	13254.6	13231.0	13161.1	13195.7	13251.5
12.5°	11197.5	11121.3	11119.7	11229.7	11214.8
15°	8482.2	8380.0	8436.6	8409.1	8394.2
17.5°	5704.0	5664.7	5740.1	5717.3	5619.2
20°	4103.2	4113.4	4257.2	4184.9	4097.7
22.5°	2994.2	3031.1	3201.5	3015.4	2947.0
25°	1993.5	2068.9	2248.0	2016.3	1952.6
27.5°	1226.1	1260.7	1442.1	1210.4	1175.8
30°	762.7	745.4	831.0	713.2	664.5
32.5°	500.3	478.3	505.8	454.0	414.7
35°	334.6	341.7	320.5	318.1	268.6
37.5°	208.9	240.4	212.1	226.2	172.8
40°	135.1	174.4	150.0	165.7	127.2
42.5°	110.7	134.3	123.3	131.2	113.1
45°	88.0	109.2	109.2	109.2	88.8
47.5°	48.7	73.0	93.5	74.6	51.8
50°	27.5	36.9	72.3	38.5	29.1
52.5°	18.9	21.2	49.5	22.0	19.6
55°	14.1	14.9	26.7	15.7	14.9
57.5°	11.0	11.8	14.1	11.8	11.0
60°	8.6	8.6	10.2	9.4	8.6
62.5°	6.3	6.3	7.1	6.3	6.3
65°	4.7	4.7	4.7	4.7	4.7
67.5°	2.4	3.1	3.1	3.1	3.1
70°	2.4	1.6	1.6	1.6	2.4
72.5°	1.6	0.8	0.8	0.8	0.8
75°	0.0	0.0	0.8	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)