

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769984

Luminaire Tested: LD6D65D010-EU6DR6055659030-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769984
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR6055659030-6LBCSSQMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7738.5 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P769984

CATALOG NUMBER: LD6D65D010-EU6DR6055659030-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P769984

CATALOG NUMBER: LD6D65D010-EU6DR6055659030-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87	85	82	81
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82	79	77	75
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78	74	71	70
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74	70	67	65
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69	65	62	61
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66	61	58	57
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62	58	55	53
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59	55	52	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	846137
5°	844061
10°	872104
15°	872999
20°	803259
25°	683226
30°	520588
35°	368136
40°	216184
45°	87225
50°	29117
55°	14020
60°	5769
65°	853
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 87225 cd/sqm



TEST NUMBER: P769984

CATALOG NUMBER: LD6D65D010-EU6DR6055659030-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	742.4	9.6
10°-20°	2138.1	27.6
20°-30°	2559.0	33.1
30°-40°	1711.6	22.1
40°-50°	507.5	6.6
50°-60°	73.0	0.9
60°-70°	6.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5439.5	70.3
0°-40°	7151.1	92.4
0°-60°	7731.5	99.9
0°-90°	7738.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7738.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7744	
5°	7696	742
15°	7718	2138
25°	5667	2559
35°	2760	1712
45°	564	507
55°	74	73
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P769984

CATALOG NUMBER: LD6D65D010-EU6DR6055659030-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	7744.2
2.5°	7734.3
5°	7695.8
7.5°	7800.2
10°	7860.6
12.5°	7849.6
15°	7717.8
17.5°	7407.0
20°	6908.4
22.5°	6309.8
25°	5667.3
27.5°	4943.5
30°	4126.3
32.5°	3397.1
35°	2760.0
37.5°	2121.9
40°	1515.7
42.5°	999.5
45°	564.5
47.5°	288.9
50°	171.3
52.5°	110.9
55°	73.6
57.5°	47.2
60°	26.4
62.5°	11.0
65°	3.3
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)