

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769543

Luminaire Tested: LD6D65D010-EU6DR3055659040-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769543
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR3055659040-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7470.7 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P769543

CATALOG NUMBER: LD6D65D010-EU6DR3055659040-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P769543

CATALOG NUMBER: LD6D65D010-EU6DR3055659040-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1838725	1838725	1838725
5°	1785940	1783858	1786032
10°	1546890	1535986	1546525
15°	1009270	1003849	998802
20°	501865	520690	501189
25°	252803	285074	247626
30°	101218	110286	88190
35°	46945	44964	37695
40°	20274	22512	19095
45°	14300	17742	14430
50°	4918	12920	5192
55°	2829	5351	2989
60°	1990	2342	1990
65°	1286	1286	1286
70°	783	537	783
75°	0	355	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 17742 cd/sqm



TEST NUMBER: P769543

CATALOG NUMBER: LD6D65D010-EU6DR3055659040-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2112.4	28.3
10°-20°	3402.0	45.5
20°-30°	1470.1	19.7
30°-40°	335.1	4.5
40°-50°	115.0	1.5
50°-60°	28.1	0.4
60°-70°	7.3	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6984.4	93.5
0°-40°	7319.5	98.0
0°-60°	7462.7	99.9
0°-90°	7470.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7470.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	24022	24022	24022	24022	24022	
5°	23244	23221	23216	23265	23245	2114
15°	12736	12583	12668	12627	12604	3410
25°	2993	3106	3375	3028	2932	1433
35°	502	513	481	478	403	341
45°	132	164	164	164	133	94
55°	21	22	40	24	22	21
65°	7	7	7	7	7	7
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P769543

CATALOG NUMBER: LD6D65D010-EU6DR3055659040-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	24022.0	24022.0	24022.0	24022.0	24022.0
2.5°	23862.8	23846.3	23855.7	23867.5	23872.2
5°	23243.6	23221.2	23216.5	23264.8	23244.8
7.5°	21994.6	21962.8	21914.4	22024.1	22126.7
10°	19902.3	19867.0	19762.0	19813.9	19897.6
12.5°	16813.5	16699.1	16696.7	16861.9	16839.4
15°	12736.3	12583.0	12667.9	12626.6	12604.2
17.5°	8564.8	8505.8	8619.0	8584.8	8437.4
20°	6161.2	6176.5	6392.3	6283.8	6152.9
22.5°	4495.9	4551.3	4807.2	4527.7	4425.1
25°	2993.3	3106.5	3375.4	3027.5	2932.0
27.5°	1841.0	1892.9	2165.4	1817.5	1765.6
30°	1145.2	1119.2	1247.8	1070.9	997.8
32.5°	751.3	718.3	759.5	681.7	622.7
35°	502.4	513.0	481.2	477.7	403.4
37.5°	313.7	360.9	318.4	339.7	259.5
40°	202.9	261.8	225.3	248.9	191.1
42.5°	166.3	201.7	185.2	197.0	169.8
45°	132.1	163.9	163.9	163.9	133.3
47.5°	73.1	109.7	140.3	112.0	77.8
50°	41.3	55.4	108.5	57.8	43.6
52.5°	28.3	31.8	74.3	33.0	29.5
55°	21.2	22.4	40.1	23.6	22.4
57.5°	16.5	17.7	21.2	17.7	16.5
60°	13.0	13.0	15.3	14.2	13.0
62.5°	9.4	9.4	10.6	9.4	9.4
65°	7.1	7.1	7.1	7.1	7.1
67.5°	3.5	4.7	4.7	4.7	4.7
70°	3.5	2.4	2.4	2.4	3.5
72.5°	2.4	1.2	1.2	1.2	1.2
75°	0.0	0.0	1.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)