

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770282

Luminaire Tested: LD6D70BD010-EU6DR3070959027-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770282
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR3070959027-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6986.8 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P770282

CATALOG NUMBER: LD6D70BD010-EU6DR3070959027-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P770282

CATALOG NUMBER: LD6D70BD010-EU6DR3070959027-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1719632	1719632	1719632
5°	1670264	1668312	1670348
10°	1446704	1436499	1446362
15°	943902	938830	934115
20°	469356	486967	468729
25°	236427	266612	231588
30°	94660	103145	82472
35°	43909	42049	35246
40°	18955	21053	17856
45°	13369	16595	13488
50°	4597	12087	4858
55°	2656	5004	2802
60°	1852	2189	1852
65°	1195	1195	1195
70°	739	492	739
75°	0	325	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 16595 cd/sqm



TEST NUMBER: P770282

CATALOG NUMBER: LD6D70BD010-EU6DR3070959027-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1975.6	28.3
10°-20°	3181.6	45.5
20°-30°	1374.9	19.7
30°-40°	313.4	4.5
40°-50°	107.6	1.5
50°-60°	26.3	0.4
60°-70°	6.8	0.1
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6532.1	93.5
0°-40°	6845.4	98.0
0°-60°	6979.3	99.9
0°-90°	6986.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6986.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	22466	22466	22466	22466	22466	
5°	21738	21717	21713	21758	21739	1977
15°	11911	11768	11847	11809	11788	3189
25°	2799	2905	3157	2831	2742	1340
35°	470	480	450	447	377	319
45°	124	153	153	153	125	88
55°	20	21	38	22	21	19
65°	7	7	7	7	7	6
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P770282

CATALOG NUMBER: LD6D70BD010-EU6DR3070959027-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	22466.1	22466.1	22466.1	22466.1	22466.1
2.5°	22317.2	22301.8	22310.6	22321.6	22326.0
5°	21738.1	21717.2	21712.7	21758.0	21739.2
7.5°	20570.0	20540.2	20495.0	20597.6	20693.6
10°	18613.3	18580.2	18482.0	18530.6	18608.9
12.5°	15724.5	15617.5	15615.3	15769.7	15748.8
15°	11911.4	11768.0	11847.4	11808.8	11787.9
17.5°	8010.1	7954.9	8060.8	8028.8	7890.9
20°	5762.1	5776.5	5978.3	5876.8	5754.4
22.5°	4204.7	4256.5	4495.9	4234.5	4138.5
25°	2799.4	2905.3	3156.8	2831.4	2742.1
27.5°	1721.8	1770.3	2025.1	1699.7	1651.2
30°	1071.0	1046.8	1167.0	1001.5	933.1
32.5°	702.6	671.7	710.3	637.5	582.4
35°	469.9	479.8	450.0	446.7	377.2
37.5°	293.4	337.5	297.8	317.7	242.7
40°	189.7	244.9	210.7	232.7	178.7
42.5°	155.5	188.6	173.2	184.2	158.8
45°	123.5	153.3	153.3	153.3	124.6
47.5°	68.4	102.6	131.3	104.8	72.8
50°	38.6	51.8	101.5	54.0	40.8
52.5°	26.5	29.8	69.5	30.9	27.6
55°	19.9	21.0	37.5	22.1	21.0
57.5°	15.4	16.5	19.9	16.5	15.4
60°	12.1	12.1	14.3	13.2	12.1
62.5°	8.8	8.8	9.9	8.8	8.8
65°	6.6	6.6	6.6	6.6	6.6
67.5°	3.3	4.4	4.4	4.4	4.4
70°	3.3	2.2	2.2	2.2	3.3
72.5°	2.2	1.1	1.1	1.1	1.1
75°	0.0	0.0	1.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)