

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770765

Luminaire Tested: LD6D70BD010-EU6DR6070959030-6LBCSSQMW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P770765  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D70BD010-EU6DR6070959030-6LBCSSQMW  
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7941.2 lumens  
Efficiency: N/A  
Efficacy: 119.2 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 66.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P770765  
CATALOG NUMBER: LD6D70BD010-EU6DR6070959030-6LBCSSQMW

### Luminous Intensity Polar Plot





TEST NUMBER: P770765

CATALOG NUMBER: LD6D70BD010-EU6DR6070959030-6LBCSSQMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70
6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	868306
5°	866183
10°	894959
15°	895871
20°	824305
25°	701129
30°	534239
35°	377793
40°	221846
45°	89512
50°	29882
55°	14382
60°	5922
65°	879
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 89512 cd/sqm



TEST NUMBER: P770765

CATALOG NUMBER: LD6D70BD010-EU6DR6070959030-6LBCSSQMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	761.8	9.6
10°-20°	2194.1	27.6
20°-30°	2626.1	33.1
30°-40°	1756.4	22.1
40°-50°	520.7	6.6
50°-60°	74.9	0.9
60°-70°	7.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5582.1	70.3
0°-40°	7338.5	92.4
0°-60°	7934.1	99.9
0°-90°	7941.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7941.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7947	
5°	7898	762
15°	7920	2194
25°	5816	2626
35°	2832	1756
45°	579	521
55°	76	75
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P770765

CATALOG NUMBER: LD6D70BD010-EU6DR6070959030-6LBCSSQMW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7947.1
2.5°	7936.9
5°	7897.5
7.5°	8004.6
10°	8066.6
12.5°	8055.3
15°	7920.0
17.5°	7601.1
20°	7089.4
22.5°	6475.1
25°	5815.8
27.5°	5073.0
30°	4234.5
32.5°	3486.1
35°	2832.4
37.5°	2177.5
40°	1555.4
42.5°	1025.6
45°	579.3
47.5°	296.4
50°	175.8
52.5°	113.8
55°	75.5
57.5°	48.5
60°	27.1
62.5°	11.3
65°	3.4
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)