

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771622

Luminaire Tested: LD6D75BD010-EU6DR6570959030-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P771622
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR6570959030-6LBCSSQMMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7507.2 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P771622
CATALOG NUMBER: LD6D75BD010-EU6DR6570959030-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P771622

CATALOG NUMBER: LD6D75BD010-EU6DR6570959030-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	398098
5°	397092
10°	396755
15°	384528
20°	350065
25°	305060
30°	253719
35°	201039
40°	145102
45°	91665
50°	47783
55°	25395
60°	13339
65°	7338
70°	3074
75°	3385
80°	2354
85°	2010

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 91665 cd/sqm



TEST NUMBER: P771622

CATALOG NUMBER: LD6D75BD010-EU6DR6570959030-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	644.6	8.6
10°-20°	1765.2	23.5
20°-30°	2157.6	28.7
30°-40°	1750.7	23.3
40°-50°	872.4	11.6
50°-60°	243.3	3.2
60°-70°	55.3	0.7
70°-80°	14.4	0.2
80°-90°	3.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4567.4	60.8
0°-40°	6318.1	84.2
0°-60°	7433.8	99.0
0°-90°	7507.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7507.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6816	
5°	6773	645
15°	6360	1765
25°	4734	2158
35°	2820	1751
45°	1110	872
55°	249	243
65°	53	55
75°	15	14
85°	3	4
90°	0	



TEST NUMBER: P771622

CATALOG NUMBER: LD6D75BD010-EU6DR6570959030-6LBCSSQMMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	6816.3
2.5°	6811.3
5°	6773.2
7.5°	6751.2
10°	6690.1
12.5°	6565.9
15°	6359.6
17.5°	6037.0
20°	5632.4
22.5°	5195.6
25°	4733.9
27.5°	4240.0
30°	3762.2
32.5°	3290.5
35°	2819.7
37.5°	2349.9
40°	1903.2
42.5°	1484.5
45°	1109.8
47.5°	773.3
50°	525.9
52.5°	362.6
55°	249.4
57.5°	168.3
60°	114.2
62.5°	79.1
65°	53.1
67.5°	27.0
70°	18.0
72.5°	17.0
75°	15.0
77.5°	10.0
80°	7.0
82.5°	5.0
85°	3.0
87.5°	2.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)