

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773936

Luminaire Tested: LD6D90BD010-EU6DR6570959024-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773936
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR6570959024-6LBCSSQMMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8230.8 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773936
CATALOG NUMBER: LD6D90BD010-EU6DR6570959024-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P773936

CATALOG NUMBER: LD6D90BD010-EU6DR6570959024-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	436470
5°	435370
10°	434995
15°	421586
20°	383802
25°	334458
30°	278179
35°	220418
40°	159084
45°	100502
50°	52390
55°	27849
60°	14624
65°	8043
70°	3381
75°	3723
80°	2590
85°	2211

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 100502 cd/sqm



TEST NUMBER: P773936

CATALOG NUMBER: LD6D90BD010-EU6DR6570959024-6LBCSSQMMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	706.7	8.6
10°-20°	1935.3	23.5
20°-30°	2365.6	28.7
30°-40°	1919.4	23.3
40°-50°	956.5	11.6
50°-60°	266.8	3.2
60°-70°	60.7	0.7
70°-80°	15.8	0.2
80°-90°	4.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5007.7	60.8
0°-40°	6927.1	84.2
0°-60°	8150.3	99.0
0°-90°	8230.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8230.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7473	
5°	7426	707
15°	6972	1935
25°	5190	2366
35°	3092	1919
45°	1217	956
55°	274	267
65°	58	61
75°	16	16
85°	3	4
90°	0	



TEST NUMBER: P773936

CATALOG NUMBER: LD6D90BD010-EU6DR6570959024-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	7473.3
2.5°	7467.8
5°	7426.1
7.5°	7401.9
10°	7334.9
12.5°	7198.8
15°	6972.5
17.5°	6618.9
20°	6175.2
22.5°	5696.4
25°	5190.1
27.5°	4648.7
30°	4124.9
32.5°	3607.6
35°	3091.5
37.5°	2576.4
40°	2086.6
42.5°	1627.5
45°	1216.8
47.5°	847.8
50°	576.6
52.5°	397.6
55°	273.5
57.5°	184.5
60°	125.2
62.5°	86.8
65°	58.2
67.5°	29.7
70°	19.8
72.5°	18.7
75°	16.5
77.5°	11.0
80°	7.7
82.5°	5.5
85°	3.3
87.5°	2.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)