

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774742

Luminaire Tested: LD6D95BD010-EU6DR6570959030-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774742
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6570959030-6LBCSSQMMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9838.4 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774742

CATALOG NUMBER: LD6D95BD010-EU6DR6570959030-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P774742

CATALOG NUMBER: LD6D95BD010-EU6DR6570959030-6LBCSSQMMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	521722
5°	520408
10°	519961
15°	503932
20°	458770
25°	399789
30°	332515
35°	263467
40°	190160
45°	120135
50°	62621
55°	33286
60°	17474
65°	9618
70°	4030
75°	4445
80°	3094
85°	2613

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 120135 cd/sqm



TEST NUMBER: P774742

CATALOG NUMBER: LD6D95BD010-EU6DR6570959030-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	844.8	8.6
10°-20°	2313.3	23.5
20°-30°	2827.7	28.7
30°-40°	2294.3	23.3
40°-50°	1143.3	11.6
50°-60°	318.9	3.2
60°-70°	72.5	0.7
70°-80°	18.8	0.2
80°-90°	4.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5985.8	60.8
0°-40°	8280.1	84.2
0°-60°	9742.3	99.0
0°-90°	9838.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9838.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8933	
5°	8877	845
15°	8334	2313
25°	6204	2828
35°	3695	2294
45°	1454	1143
55°	327	319
65°	70	72
75°	20	19
85°	4	5
90°	0	



TEST NUMBER: P774742

CATALOG NUMBER: LD6D95BD010-EU6DR6570959030-6LBCSSQMMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	8933.0
2.5°	8926.5
5°	8876.6
7.5°	8847.7
10°	8767.6
12.5°	8604.8
15°	8334.4
17.5°	7911.7
20°	7381.4
22.5°	6809.0
25°	6203.9
27.5°	5556.7
30°	4930.6
32.5°	4312.3
35°	3695.3
37.5°	3079.6
40°	2494.2
42.5°	1945.4
45°	1454.5
47.5°	1013.4
50°	689.2
52.5°	475.2
55°	326.9
57.5°	220.5
60°	149.6
62.5°	103.7
65°	69.6
67.5°	35.4
70°	23.6
72.5°	22.3
75°	19.7
77.5°	13.1
80°	9.2
82.5°	6.6
85°	3.9
87.5°	2.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)