

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774753

Luminaire Tested: LD6D95BD010-EU6DR6570959030-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P774753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6570959030-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8813.6 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774753
CATALOG NUMBER: LD6D95BD010-EU6DR6570959030-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774753

CATALOG NUMBER: LD6D95BD010-EU6DR6570959030-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	948121
5°	948902
10°	982318
15°	983943
20°	905882
25°	771859
30°	590887
35°	417448
40°	246407
45°	100035
50°	36257
55°	20211
60°	11582
65°	6386
70°	6709
75°	5192
80°	5411
85°	4638

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 100035 cd/sqm



TEST NUMBER: P774753

CATALOG NUMBER: LD6D95BD010-EU6DR6570959030-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	835.6	9.5
10°-20°	2410.3	27.3
20°-30°	2891.9	32.8
30°-40°	1943.4	22.1
40°-50°	581.8	6.6
50°-60°	102.7	1.2
60°-70°	29.2	0.3
70°-80°	14.3	0.2
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6137.7	69.6
0°-40°	8081.1	91.7
0°-60°	8765.6	99.5
0°-90°	8813.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8813.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8678	
5°	8652	836
15°	8699	2410
25°	6402	2892
35°	3130	1943
45°	647	582
55°	106	103
65°	25	29
75°	12	14
85°	4	5
90°	0	



TEST NUMBER: P774753

CATALOG NUMBER: LD6D95BD010-EU6DR6570959030-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	8677.6
2.5°	8714.6
5°	8651.7
7.5°	8782.4
10°	8854.0
12.5°	8836.7
15°	8698.6
17.5°	8360.7
20°	7791.0
22.5°	7120.2
25°	6402.5
27.5°	5592.3
30°	4683.5
32.5°	3859.7
35°	3129.7
37.5°	2408.3
40°	1727.6
42.5°	1128.3
45°	647.4
47.5°	342.8
50°	213.3
52.5°	148.0
55°	106.1
57.5°	76.5
60°	53.0
62.5°	34.5
65°	24.7
67.5°	22.2
70°	21.0
72.5°	16.0
75°	12.3
77.5°	11.1
80°	8.6
82.5°	6.2
85°	3.7
87.5°	2.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)