

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P787444

Luminaire Tested: LER6D02D010-EC6DR650210IC9040-6LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P787444  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D02D010-EC6DR650210IC9040-6LBS1H  
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 633.0 lumens  
Efficiency: N/A  
Efficacy: 124.1 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 5.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P787444  
CATALOG NUMBER: LER6D02D010-EC6DR650210IC9040-6LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P787444

CATALOG NUMBER: LER6D02D010-EC6DR650210IC9040-6LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	33571
5°	33482
10°	33454
15°	32421
20°	29516
25°	25725
30°	21392
35°	16955
40°	12237
45°	7731
50°	4025
55°	2138
60°	1121
65°	622
70°	256
75°	293
80°	202
85°	201

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7731 cd/sqm



TEST NUMBER: P787444

CATALOG NUMBER: LER6D02D010-EC6DR650210IC9040-6LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.4	8.6
10°-20°	148.8	23.5
20°-30°	181.9	28.7
30°-40°	147.6	23.3
40°-50°	73.6	11.6
50°-60°	20.5	3.2
60°-70°	4.7	0.7
70°-80°	1.2	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	385.1	60.8
0°-40°	532.7	84.2
0°-60°	626.8	99.0
0°-90°	633.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	633.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	575	
5°	571	54
15°	536	149
25°	399	182
35°	238	148
45°	94	74
55°	21	21
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P787444

CATALOG NUMBER: LER6D02D010-EC6DR650210IC9040-6LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	574.8
2.5°	574.3
5°	571.1
7.5°	569.3
10°	564.1
12.5°	553.6
15°	536.2
17.5°	509.0
20°	474.9
22.5°	438.1
25°	399.2
27.5°	357.5
30°	317.2
32.5°	277.5
35°	237.8
37.5°	198.1
40°	160.5
42.5°	125.2
45°	93.6
47.5°	65.2
50°	44.3
52.5°	30.6
55°	21.0
57.5°	14.2
60°	9.6
62.5°	6.7
65°	4.5
67.5°	2.3
70°	1.5
72.5°	1.4
75°	1.3
77.5°	0.8
80°	0.6
82.5°	0.4
85°	0.3
87.5°	0.2
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)