

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790518

Luminaire Tested: LER6D20D010-EC6DR6520359024-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P790518
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D20D010-EC6DR6520359024-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2559.3 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P790518

CATALOG NUMBER: LER6D20D010-EC6DR6520359024-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P790518

CATALOG NUMBER: LER6D20D010-EC6DR6520359024-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	135719
5°	135376
10°	135262
15°	131092
20°	119344
25°	104002
30°	86497
35°	68539
40°	49465
45°	31254
50°	16291
55°	8655
60°	4544
65°	2501
70°	1042
75°	1151
80°	807
85°	670

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 31254 cd/sqm



TEST NUMBER: P790518

CATALOG NUMBER: LER6D20D010-EC6DR6520359024-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.8	8.6
10°-20°	601.8	23.5
20°-30°	735.6	28.7
30°-40°	596.8	23.3
40°-50°	297.4	11.6
50°-60°	83.0	3.2
60°-70°	18.8	0.7
70°-80°	4.9	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1557.1	60.8
0°-40°	2154.0	84.2
0°-60°	2534.3	99.0
0°-90°	2559.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2559.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2324	
5°	2309	220
15°	2168	602
25°	1614	736
35°	961	597
45°	378	297
55°	85	83
65°	18	19
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P790518

CATALOG NUMBER: LER6D20D010-EC6DR6520359024-6LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2323.8
2.5°	2322.1
5°	2309.1
7.5°	2301.6
10°	2280.8
12.5°	2238.4
15°	2168.1
17.5°	2058.1
20°	1920.2
22.5°	1771.3
25°	1613.9
27.5°	1445.5
30°	1282.6
32.5°	1121.8
35°	961.3
37.5°	801.1
40°	648.8
42.5°	506.1
45°	378.4
47.5°	263.6
50°	179.3
52.5°	123.6
55°	85.0
57.5°	57.4
60°	38.9
62.5°	27.0
65°	18.1
67.5°	9.2
70°	6.1
72.5°	5.8
75°	5.1
77.5°	3.4
80°	2.4
82.5°	1.7
85°	1.0
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)