

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790763

Luminaire Tested: LER6D25D010-EC6DR3020359027-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P790763
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR3020359027-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4619.3 lumens
Efficiency: N/A
Efficacy: 184.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P790763

CATALOG NUMBER: LER6D25D010-EC6DR3020359027-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P790763

CATALOG NUMBER: LER6D25D010-EC6DR3020359027-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1136914	1136914	1136914
5°	1104276	1102985	1104330
10°	956474	949728	956241
15°	624051	620699	617577
20°	310314	321954	309899
25°	156312	176269	153111
30°	62585	68189	54525
35°	29033	27799	23304
40°	12530	13919	11801
45°	8844	10976	8920
50°	3037	7990	3215
55°	1748	3310	1855
60°	1225	1454	1225
65°	797	797	797
70°	492	336	492
75°	0	207	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 10976 cd/sqm



TEST NUMBER: P790763

CATALOG NUMBER: LER6D25D010-EC6DR3020359027-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1306.1	28.3
10°-20°	2103.5	45.5
20°-30°	909.0	19.7
30°-40°	207.2	4.5
40°-50°	71.1	1.5
50°-60°	17.4	0.4
60°-70°	4.5	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4318.6	93.5
0°-40°	4525.8	98.0
0°-60°	4614.3	99.9
0°-90°	4619.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4619.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	14853	14853	14853	14853	14853	
5°	14372	14358	14355	14385	14373	1307
15°	7875	7780	7833	7807	7793	2109
25°	1851	1921	2087	1872	1813	886
35°	311	317	298	295	249	211
45°	82	101	101	101	82	58
55°	13	14	25	15	14	13
65°	4	4	4	4	4	4
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P790763

CATALOG NUMBER: LER6D25D010-EC6DR3020359027-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	14853.2	14853.2	14853.2	14853.2	14853.2
2.5°	14754.8	14744.5	14750.4	14757.7	14760.6
5°	14371.9	14358.0	14355.1	14385.0	14372.6
7.5°	13599.6	13579.9	13550.0	13617.9	13681.3
10°	12306.0	12284.1	12219.2	12251.3	12303.0
12.5°	10396.1	10325.3	10323.9	10426.0	10412.1
15°	7875.1	7780.3	7832.8	7807.3	7793.4
17.5°	5295.8	5259.3	5329.3	5308.2	5217.0
20°	3809.6	3819.0	3952.5	3885.4	3804.5
22.5°	2779.9	2814.1	2972.4	2799.6	2736.1
25°	1850.8	1920.8	2087.1	1872.0	1812.9
27.5°	1138.3	1170.4	1338.9	1123.8	1091.7
30°	708.1	692.1	771.5	662.2	616.9
32.5°	464.5	444.1	469.6	421.5	385.0
35°	310.7	317.2	297.5	295.3	249.4
37.5°	194.0	223.1	196.9	210.0	160.4
40°	125.4	161.9	139.3	153.9	118.1
42.5°	102.8	124.7	114.5	121.8	105.0
45°	81.7	101.4	101.4	101.4	82.4
47.5°	45.2	67.8	86.8	69.3	48.1
50°	25.5	34.3	67.1	35.7	27.0
52.5°	17.5	19.7	45.9	20.4	18.2
55°	13.1	13.9	24.8	14.6	13.9
57.5°	10.2	10.9	13.1	10.9	10.2
60°	8.0	8.0	9.5	8.8	8.0
62.5°	5.8	5.8	6.6	5.8	5.8
65°	4.4	4.4	4.4	4.4	4.4
67.5°	2.2	2.9	2.9	2.9	2.9
70°	2.2	1.5	1.5	1.5	2.2
72.5°	1.5	0.7	0.7	0.7	0.7
75°	0.0	0.0	0.7	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)