

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790777

Luminaire Tested: LER6D25D010-EC6DR3020359035-6LBDP1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P790777  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D25D010-EC6DR3020359035-6LBDDP1LI  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 30° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5357.0 lumens  
Efficiency: N/A  
Efficacy: 213.4 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49  
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P790777

CATALOG NUMBER: LER6D25D010-EC6DR3020359035-6LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P790777

CATALOG NUMBER: LER6D25D010-EC6DR3020359035-6LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1318491	1318491	1318491
5°	1280645	1279147	1280706
10°	1109233	1101406	1108969
15°	723716	719833	716211
20°	359872	373377	359391
25°	181277	204418	177561
30°	72582	79087	63239
35°	33667	32238	27023
40°	14538	16137	13689
45°	10251	12730	10349
50°	3525	9264	3727
55°	2028	3843	2149
60°	1424	1684	1424
65°	924	924	924
70°	559	380	559
75°	0	237	0
80°	0	0	0
85°	0	0	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 12730 cd/sqm



TEST NUMBER: P790777

CATALOG NUMBER: LER6D25D010-EC6DR3020359035-6LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1514.7	28.3
10°-20°	2439.5	45.5
20°-30°	1054.2	19.7
30°-40°	240.3	4.5
40°-50°	82.5	1.5
50°-60°	20.1	0.4
60°-70°	5.2	0.1
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5008.3	93.5
0°-40°	5248.6	98.0
0°-60°	5351.2	99.9
0°-90°	5357.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5357.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	17225	17225	17225	17225	17225	
5°	16667	16651	16648	16682	16668	1516
15°	9133	9023	9084	9054	9038	2445
25°	2146	2228	2420	2171	2102	1027
35°	360	368	345	342	289	244
45°	95	118	118	118	96	67
55°	15	16	29	17	16	15
65°	5	5	5	5	5	5
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P790777

CATALOG NUMBER: LER6D25D010-EC6DR3020359035-6LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	17225.4	17225.4	17225.4	17225.4	17225.4
2.5°	17111.3	17099.4	17106.2	17114.6	17118.0
5°	16667.3	16651.2	16647.8	16682.5	16668.1
7.5°	15771.7	15748.8	15714.1	15792.8	15866.4
10°	14271.4	14246.0	14170.7	14207.9	14268.0
12.5°	12056.4	11974.4	11972.7	12091.1	12075.1
15°	9132.8	9022.9	9083.8	9054.2	9038.1
17.5°	6141.5	6099.3	6180.5	6155.9	6050.2
20°	4418.0	4429.0	4583.8	4505.9	4412.1
22.5°	3223.8	3263.6	3447.1	3246.7	3173.1
25°	2146.4	2227.6	2420.4	2170.9	2102.4
27.5°	1320.2	1357.4	1552.7	1303.2	1266.0
30°	821.2	802.6	894.8	767.9	715.5
32.5°	538.7	515.0	544.6	488.8	446.5
35°	360.3	367.9	345.0	342.5	289.2
37.5°	225.0	258.8	228.3	243.6	186.1
40°	145.5	187.7	161.5	178.4	137.0
42.5°	119.2	144.6	132.8	141.2	121.8
45°	94.7	117.6	117.6	117.6	95.6
47.5°	52.4	78.7	100.6	80.3	55.8
50°	29.6	39.7	77.8	41.4	31.3
52.5°	20.3	22.8	53.3	23.7	21.1
55°	15.2	16.1	28.8	16.9	16.1
57.5°	11.8	12.7	15.2	12.7	11.8
60°	9.3	9.3	11.0	10.1	9.3
62.5°	6.8	6.8	7.6	6.8	6.8
65°	5.1	5.1	5.1	5.1	5.1
67.5°	2.5	3.4	3.4	3.4	3.4
70°	2.5	1.7	1.7	1.7	2.5
72.5°	1.7	0.8	0.8	0.8	0.8
75°	0.0	0.0	0.8	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)