

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P790933

Luminaire Tested: LER6D25D010-EC6DR4520359040-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P790933
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR4520359040-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6077.8 lumens
Efficiency: N/A
Efficacy: 242.1 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P790933
CATALOG NUMBER: LER6D25D010-EC6DR4520359040-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P790933
 CATALOG NUMBER: LER6D25D010-EC6DR4520359040-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95				
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90				
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85				
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81				
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77				
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73				
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69				
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66				
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63				
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1173756
5°	1140334
10°	1090990
15°	998489
20°	792144
25°	494544
30°	272576
35°	122392
40°	48209
45°	22714
50°	10777
55°	5639
60°	2775
65°	646
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22714 cd/sqm



TEST NUMBER: P790933

CATALOG NUMBER: LER6D25D010-EC6DR4520359040-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	976.9	16.1
10°-20°	2404.3	39.6
20°-30°	1903.9	31.3
30°-40°	634.0	10.4
40°-50°	125.8	2.1
50°-60°	28.6	0.5
60°-70°	4.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5285.1	87.0
0°-40°	5919.2	97.4
0°-60°	6073.6	99.9
0°-90°	6077.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6077.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10743	
5°	10397	977
15°	8827	2404
25°	4102	1904
35°	918	634
45°	147	126
55°	30	29
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P790933

CATALOG NUMBER: LER6D25D010-EC6DR4520359040-6LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	10742.7
2.5°	10672.5
5°	10397.1
7.5°	10169.8
10°	9833.5
12.5°	9385.7
15°	8827.2
17.5°	7987.3
20°	6812.8
22.5°	5413.6
25°	4102.2
27.5°	3003.8
30°	2160.5
32.5°	1469.4
35°	917.6
37.5°	544.1
40°	338.0
42.5°	222.2
45°	147.0
47.5°	94.6
50°	63.4
52.5°	42.2
55°	29.6
57.5°	19.4
60°	12.7
62.5°	6.8
65°	2.5
67.5°	0.8
70°	0.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)