

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791119

Luminaire Tested: LER6D25D010-EC6DR6520359040-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P791119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR6520359040-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3504.4 lumens
Efficiency: N/A
Efficacy: 139.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P791119

CATALOG NUMBER: LER6D25D010-EC6DR6520359040-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P791119

CATALOG NUMBER: LER6D25D010-EC6DR6520359040-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	376982
5°	377293
10°	390575
15°	391231
20°	360190
25°	306899
30°	234942
35°	165981
40°	97972
45°	39773
50°	14414
55°	8039
60°	4611
65°	2534
70°	2651
75°	2069
80°	2139
85°	1880

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 39773 cd/sqm



TEST NUMBER: P791119

CATALOG NUMBER: LER6D25D010-EC6DR6520359040-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.2	9.5
10°-20°	958.4	27.3
20°-30°	1149.9	32.8
30°-40°	772.7	22.1
40°-50°	231.3	6.6
50°-60°	40.8	1.2
60°-70°	11.6	0.3
70°-80°	5.7	0.2
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2440.4	69.6
0°-40°	3213.2	91.7
0°-60°	3485.3	99.5
0°-90°	3504.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3504.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3450	
5°	3440	332
15°	3459	958
25°	2546	1150
35°	1244	773
45°	257	231
55°	42	41
65°	10	12
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P791119

CATALOG NUMBER: LER6D25D010-EC6DR6520359040-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3450.3
2.5°	3465.0
5°	3440.0
7.5°	3492.0
10°	3520.4
12.5°	3513.6
15°	3458.7
17.5°	3324.3
20°	3097.8
22.5°	2831.1
25°	2545.7
27.5°	2223.6
30°	1862.2
32.5°	1534.7
35°	1244.4
37.5°	957.6
40°	686.9
42.5°	448.6
45°	257.4
47.5°	136.3
50°	84.8
52.5°	58.8
55°	42.2
57.5°	30.4
60°	21.1
62.5°	13.7
65°	9.8
67.5°	8.8
70°	8.3
72.5°	6.4
75°	4.9
77.5°	4.4
80°	3.4
82.5°	2.5
85°	1.5
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)