

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791132

Luminaire Tested: LER6D25D010-EC6DR6520359050-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791132
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR6520359050-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4893.8 lumens
Efficiency: N/A
Efficacy: 195.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791132
CATALOG NUMBER: LER6D25D010-EC6DR6520359050-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P791132
 CATALOG NUMBER: LER6D25D010-EC6DR6520359050-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	259512
5°	258856
10°	258634
15°	250666
20°	228198
25°	198860
30°	165394
35°	131053
40°	94584
45°	59758
50°	31147
55°	16557
60°	8690
65°	4782
70°	2015
75°	2211
80°	1547
85°	1340

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 59758 cd/sqm



TEST NUMBER: P791132

CATALOG NUMBER: LER6D25D010-EC6DR6520359050-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	420.2	8.6
10°-20°	1150.7	23.5
20°-30°	1406.5	28.7
30°-40°	1141.2	23.3
40°-50°	568.7	11.6
50°-60°	158.6	3.2
60°-70°	36.0	0.7
70°-80°	9.4	0.2
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2977.4	60.8
0°-40°	4118.6	84.2
0°-60°	4846.0	99.0
0°-90°	4893.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4893.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4443	
5°	4415	420
15°	4146	1151
25°	3086	1407
35°	1838	1141
45°	724	569
55°	163	159
65°	35	36
75°	10	9
85°	2	2
90°	0	



TEST NUMBER: P791132

CATALOG NUMBER: LER6D25D010-EC6DR6520359050-6LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4443.4
2.5°	4440.2
5°	4415.3
7.5°	4401.0
10°	4361.1
12.5°	4280.2
15°	4145.7
17.5°	3935.4
20°	3671.6
22.5°	3386.9
25°	3085.9
27.5°	2764.0
30°	2452.5
32.5°	2145.0
35°	1838.1
37.5°	1531.9
40°	1240.6
42.5°	967.7
45°	723.5
47.5°	504.1
50°	342.8
52.5°	236.4
55°	162.6
57.5°	109.7
60°	74.4
62.5°	51.6
65°	34.6
67.5°	17.6
70°	11.8
72.5°	11.1
75°	9.8
77.5°	6.5
80°	4.6
82.5°	3.3
85°	2.0
87.5°	1.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)