

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791133

Luminaire Tested: LER6D25D010-EC6DR6520359050-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791133
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D25D010-EC6DR6520359050-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5138.5 lumens
Efficiency: N/A
Efficacy: 204.7 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791133
CATALOG NUMBER: LER6D25D010-EC6DR6520359050-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P791133
 CATALOG NUMBER: LER6D25D010-EC6DR6520359050-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	272489
5°	271800
10°	271569
15°	263200
20°	239609
25°	208803
30°	173669
35°	137605
40°	99319
45°	62748
50°	32701
55°	17381
60°	9134
65°	5016
70°	2100
75°	2324
80°	1614
85°	1407

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 62748 cd/sqm



TEST NUMBER: P791133

CATALOG NUMBER: LER6D25D010-EC6DR6520359050-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	441.2	8.6
10°-20°	1208.2	23.5
20°-30°	1476.9	28.7
30°-40°	1198.3	23.3
40°-50°	597.1	11.6
50°-60°	166.6	3.2
60°-70°	37.8	0.7
70°-80°	9.9	0.2
80°-90°	2.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3126.3	60.8
0°-40°	4324.6	84.2
0°-60°	5088.3	99.0
0°-90°	5138.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5138.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4666	
5°	4636	441
15°	4353	1208
25°	3240	1477
35°	1930	1198
45°	760	597
55°	171	167
65°	36	38
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P791133

CATALOG NUMBER: LER6D25D010-EC6DR6520359050-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4665.6
2.5°	4662.2
5°	4636.1
7.5°	4621.0
10°	4579.2
12.5°	4494.2
15°	4353.0
17.5°	4132.2
20°	3855.2
22.5°	3556.3
25°	3240.2
27.5°	2902.2
30°	2575.2
32.5°	2252.2
35°	1930.0
37.5°	1608.4
40°	1302.7
42.5°	1016.1
45°	759.7
47.5°	529.3
50°	359.9
52.5°	248.2
55°	170.7
57.5°	115.2
60°	78.2
62.5°	54.2
65°	36.3
67.5°	18.5
70°	12.3
72.5°	11.7
75°	10.3
77.5°	6.9
80°	4.8
82.5°	3.4
85°	2.1
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)