

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791183

Luminaire Tested: LER6D30D010-EC6DR1515309024-6LBDP1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P791183  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D30D010-EC6DR1515309024-6LBDDP1B  
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2624.2 lumens  
Efficiency: N/A  
Efficacy: 90.5 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P791183

CATALOG NUMBER: LER6D30D010-EC6DR1515309024-6LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P791183

CATALOG NUMBER: LER6D30D010-EC6DR1515309024-6LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4023128	4023128	4023128
5°	2364183	2333572	2352028
10°	705601	710537	721417
15°	175512	178925	173410
20°	52514	60811	53627
25°	18509	23581	18751
30°	6799	8956	6912
35°	3406	3849	3297
40°	2152	2365	2152
45°	1589	1694	1589
50°	1266	1266	1266
55°	1051	1051	1051
60°	850	850	850
65°	649	649	649
70°	556	556	556
75°	340	340	461
80°	236	236	236
85°	125	125	125

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 1694 cd/sqm



TEST NUMBER: P791183

CATALOG NUMBER: LER6D30D010-EC6DR1515309024-6LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1702.0	64.9
10°-20°	700.1	26.7
20°-30°	139.1	5.3
30°-40°	34.7	1.3
40°-50°	18.2	0.7
50°-60°	13.5	0.5
60°-70°	9.6	0.4
70°-80°	5.4	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2541.1	96.8
0°-40°	2575.8	98.2
0°-60°	2607.6	99.4
0°-90°	2624.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2624.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	35755	35755	35755	35755	35755	
5°	23263	23024	22962	23121	23143	1699
15°	2021	2058	2060	2024	1996	693
25°	238	269	303	268	241	125
35°	47	50	53	50	45	32
45°	23	23	24	23	23	18
55°	15	15	15	15	15	14
65°	9	9	9	9	9	10
75°	4	4	4	4	6	5
85°	2	2	2	2	2	2
90°	0	0	0	0	0	



TEST NUMBER: P791183

CATALOG NUMBER: LER6D30D010-EC6DR1515309024-6LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	35754.8	35754.8	35754.8	35754.8	35754.8
2.5°	32252.3	32279.5	32290.1	32321.9	32440.0
5°	23262.9	23023.7	22961.7	23120.6	23143.3
7.5°	13780.0	13828.5	14005.6	14044.9	13902.6
10°	7562.1	7624.1	7615.0	7669.5	7731.6
12.5°	3867.3	3818.9	3803.7	3865.8	3779.5
15°	2020.7	2058.5	2060.0	2023.7	1996.5
17.5°	1086.8	1130.7	1203.3	1144.3	1053.5
20°	641.8	681.1	743.2	694.8	655.4
22.5°	396.6	428.4	472.3	434.4	402.6
25°	237.6	269.4	302.7	267.9	240.7
27.5°	140.8	168.0	189.2	166.5	139.3
30°	90.8	106.0	119.6	104.4	92.3
32.5°	63.6	69.6	75.7	69.6	63.6
35°	46.9	49.9	53.0	49.9	45.4
37.5°	36.3	39.4	40.9	37.8	34.8
40°	30.3	31.8	33.3	31.8	30.3
42.5°	25.7	27.2	27.2	27.2	25.7
45°	22.7	22.7	24.2	22.7	22.7
47.5°	19.7	19.7	21.2	19.7	19.7
50°	18.2	18.2	18.2	18.2	18.2
52.5°	16.6	16.6	16.6	16.6	16.6
55°	15.1	15.1	15.1	15.1	15.1
57.5°	13.6	13.6	13.6	13.6	13.6
60°	12.1	12.1	12.1	12.1	12.1
62.5°	10.6	10.6	10.6	10.6	10.6
65°	9.1	9.1	9.1	9.1	9.1
67.5°	9.1	9.1	9.1	9.1	9.1
70°	7.6	7.6	7.6	7.6	7.6
72.5°	6.1	6.1	6.1	6.1	6.1
75°	4.5	4.5	4.5	4.5	6.1
77.5°	4.5	4.5	4.5	4.5	4.5
80°	3.0	3.0	3.0	3.0	3.0
82.5°	3.0	3.0	3.0	3.0	3.0
85°	1.5	1.5	1.5	1.5	1.5
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)