

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791349

Luminaire Tested: LER6D30D010-EC6DR3020359030-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791349
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D30D010-EC6DR3020359030-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6003.7 lumens
Efficiency: N/A
Efficacy: 207.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P791349

CATALOG NUMBER: LER6D30D010-EC6DR3020359030-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P791349

CATALOG NUMBER: LER6D30D010-EC6DR3020359030-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1477663	1477663	1477663
5°	1435239	1433564	1435315
10°	1243136	1234369	1242841
15°	811082	806731	802674
20°	403312	418446	402774
25°	203160	229096	198996
30°	81340	88632	70867
35°	37732	36134	30285
40°	16287	18086	15338
45°	11496	14256	11593
50°	3953	10384	4180
55°	2282	4297	2402
60°	1592	1883	1592
65°	1032	1032	1032
70°	627	425	627
75°	0	266	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 14256 cd/sqm



TEST NUMBER: P791349

CATALOG NUMBER: LER6D30D010-EC6DR3020359030-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1697.6	28.3
10°-20°	2734.0	45.5
20°-30°	1181.4	19.7
30°-40°	269.3	4.5
40°-50°	92.4	1.5
50°-60°	22.6	0.4
60°-70°	5.9	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5612.9	93.5
0°-40°	5882.2	98.0
0°-60°	5997.2	99.9
0°-90°	6003.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6003.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	19305	19305	19305	19305	19305	
5°	18679	18661	18658	18696	18680	1699
15°	10235	10112	10180	10147	10129	2741
25°	2406	2496	2713	2433	2356	1151
35°	404	412	387	384	324	274
45°	106	132	132	132	107	75
55°	17	18	32	19	18	17
65°	6	6	6	6	6	6
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P791349

CATALOG NUMBER: LER6D30D010-EC6DR3020359030-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	19304.9	19304.9	19304.9	19304.9	19304.9
2.5°	19176.9	19163.7	19171.2	19180.7	19184.5
5°	18679.3	18661.3	18657.5	18696.4	18680.3
7.5°	17675.6	17650.0	17611.1	17699.3	17781.8
10°	15994.2	15965.8	15881.4	15923.1	15990.4
12.5°	13511.9	13420.0	13418.1	13550.8	13532.7
15°	10235.3	10112.1	10180.4	10147.2	10129.2
17.5°	6883.0	6835.6	6926.6	6899.1	6780.6
20°	4951.3	4963.7	5137.1	5049.9	4944.7
22.5°	3613.0	3657.6	3863.2	3638.6	3556.2
25°	2405.5	2496.5	2712.6	2433.0	2356.2
27.5°	1479.5	1521.2	1740.2	1460.6	1418.9
30°	920.3	899.5	1002.8	860.6	801.8
32.5°	603.8	577.2	610.4	547.8	500.4
35°	403.8	412.3	386.7	383.9	324.1
37.5°	252.1	290.0	255.9	273.0	208.5
40°	163.0	210.4	181.0	200.0	153.5
42.5°	133.6	162.1	148.8	158.3	136.5
45°	106.2	131.7	131.7	131.7	107.1
47.5°	58.8	88.1	112.8	90.0	62.6
50°	33.2	44.5	87.2	46.4	35.1
52.5°	22.7	25.6	59.7	26.5	23.7
55°	17.1	18.0	32.2	19.0	18.0
57.5°	13.3	14.2	17.1	14.2	13.3
60°	10.4	10.4	12.3	11.4	10.4
62.5°	7.6	7.6	8.5	7.6	7.6
65°	5.7	5.7	5.7	5.7	5.7
67.5°	2.8	3.8	3.8	3.8	3.8
70°	2.8	1.9	1.9	1.9	2.8
72.5°	1.9	0.9	0.9	0.9	0.9
75°	0.0	0.0	0.9	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)