

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P791995

Luminaire Tested: LER6D35BD010-EC6DR4520359050-6LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P791995
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D35BD010-EC6DR4520359050-6LBS1B
Description: 6 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4090.4 lumens
Efficiency: N/A
Efficacy: 132.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P791995
CATALOG NUMBER: LER6D35BD010-EC6DR4520359050-6LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P791995
 CATALOG NUMBER: LER6D35BD010-EC6DR4520359050-6LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100	
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95			95	
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90			90	
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85			85	
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81			81	
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77			77	
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73			73	
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69			69	
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66			66	
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63			63	
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60			60	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	789944
5°	767451
10°	734242
15°	671994
20°	533123
25°	332831
30°	183454
35°	82377
40°	32448
45°	15282
50°	7241
55°	3791
60°	1857
65°	440
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15282 cd/sqm



TEST NUMBER: P791995

CATALOG NUMBER: LER6D35BD010-EC6DR4520359050-6LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	657.5	16.1
10°-20°	1618.1	39.6
20°-30°	1281.4	31.3
30°-40°	426.7	10.4
40°-50°	84.7	2.1
50°-60°	19.2	0.5
60°-70°	2.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3556.9	87.0
0°-40°	3983.7	97.4
0°-60°	4087.6	99.9
0°-90°	4090.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4090.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7230	
5°	6997	657
15°	5941	1618
25°	2761	1281
35°	618	427
45°	99	85
55°	20	19
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P791995

CATALOG NUMBER: LER6D35BD010-EC6DR4520359050-6LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7229.9
2.5°	7182.7
5°	6997.3
7.5°	6844.4
10°	6618.0
12.5°	6316.6
15°	5940.8
17.5°	5375.5
20°	4585.1
22.5°	3643.4
25°	2760.8
27.5°	2021.6
30°	1454.1
32.5°	988.9
35°	617.6
37.5°	366.2
40°	227.5
42.5°	149.6
45°	98.9
47.5°	63.7
50°	42.6
52.5°	28.4
55°	19.9
57.5°	13.1
60°	8.5
62.5°	4.5
65°	1.7
67.5°	0.6
70°	0.6
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)