

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P792149

Luminaire Tested: LER6D35BD010-EC6DR6520359024-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P792149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D35BD010-EC6DR6520359024-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3155.9 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 30.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P792149
CATALOG NUMBER: LER6D35BD010-EC6DR6520359024-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P792149

CATALOG NUMBER: LER6D35BD010-EC6DR6520359024-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	167356
5°	166934
10°	166789
15°	161651
20°	147158
25°	128239
30°	106661
35°	84509
40°	61000
45°	38539
50°	20089
55°	10671
60°	5607
65°	3082
70°	1298
75°	1422
80°	975
85°	871

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 38539 cd/sqm



TEST NUMBER: P792149

CATALOG NUMBER: LER6D35BD010-EC6DR6520359024-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.0	8.6
10°-20°	742.1	23.5
20°-30°	907.0	28.7
30°-40°	736.0	23.3
40°-50°	366.7	11.6
50°-60°	102.3	3.2
60°-70°	23.3	0.7
70°-80°	6.0	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1920.1	60.8
0°-40°	2656.0	84.2
0°-60°	3125.0	99.0
0°-90°	3155.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3155.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2866	
5°	2847	271
15°	2674	742
25°	1990	907
35°	1185	736
45°	467	367
55°	105	102
65°	22	23
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P792149

CATALOG NUMBER: LER6D35BD010-EC6DR6520359024-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2865.5
2.5°	2863.4
5°	2847.4
7.5°	2838.1
10°	2812.4
12.5°	2760.2
15°	2673.5
17.5°	2537.9
20°	2367.7
22.5°	2184.2
25°	1990.0
27.5°	1782.4
30°	1581.6
32.5°	1383.3
35°	1185.3
37.5°	987.9
40°	800.1
42.5°	624.0
45°	466.6
47.5°	325.1
50°	221.1
52.5°	152.4
55°	104.8
57.5°	70.7
60°	48.0
62.5°	33.3
65°	22.3
67.5°	11.4
70°	7.6
72.5°	7.2
75°	6.3
77.5°	4.2
80°	2.9
82.5°	2.1
85°	1.3
87.5°	0.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)