

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793104

Luminaire Tested: LER6D45BD010-EC6DR6540509024-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793104
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR6540509024-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3681.9 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793104

CATALOG NUMBER: LER6D45BD010-EC6DR6540509024-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P793104

CATALOG NUMBER: LER6D45BD010-EC6DR6540509024-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	396081
5°	396410
10°	410368
15°	411049
20°	378433
25°	322451
30°	246851
35°	174398
40°	102936
45°	41797
50°	15145
55°	8439
60°	4851
65°	2663
70°	2811
75°	2195
80°	2265
85°	1880

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 41797 cd/sqm



TEST NUMBER: P793104

CATALOG NUMBER: LER6D45BD010-EC6DR6540509024-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.1	9.5
10°-20°	1006.9	27.3
20°-30°	1208.1	32.8
30°-40°	811.9	22.1
40°-50°	243.0	6.6
50°-60°	42.9	1.2
60°-70°	12.2	0.3
70°-80°	6.0	0.2
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2564.1	69.6
0°-40°	3376.0	91.7
0°-60°	3661.9	99.5
0°-90°	3681.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3681.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3625	
5°	3614	349
15°	3634	1007
25°	2675	1208
35°	1308	812
45°	270	243
55°	44	43
65°	10	12
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P793104

CATALOG NUMBER: LER6D45BD010-EC6DR6540509024-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3625.1
2.5°	3640.6
5°	3614.3
7.5°	3668.9
10°	3698.8
12.5°	3691.6
15°	3633.9
17.5°	3492.7
20°	3254.7
22.5°	2974.5
25°	2674.7
27.5°	2336.2
30°	1956.6
32.5°	1612.4
35°	1307.5
37.5°	1006.1
40°	721.7
42.5°	471.4
45°	270.5
47.5°	143.2
50°	89.1
52.5°	61.8
55°	44.3
57.5°	31.9
60°	22.2
62.5°	14.4
65°	10.3
67.5°	9.3
70°	8.8
72.5°	6.7
75°	5.2
77.5°	4.6
80°	3.6
82.5°	2.6
85°	1.5
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)