

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793121

Luminaire Tested: LER6D45BD010-EC6DR6540509030-6LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793121
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR6540509030-6LBDP1LI
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4511.7 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793121

CATALOG NUMBER: LER6D45BD010-EC6DR6540509030-6LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P793121

CATALOG NUMBER: LER6D45BD010-EC6DR6540509030-6LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	485347
5°	485753
10°	502853
15°	503679
20°	463719
25°	395122
30°	302477
35°	213693
40°	126142
45°	51207
50°	18562
55°	10344
60°	5922
65°	3258
70°	3418
75°	2660
80°	2769
85°	2382

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 51207 cd/sqm



TEST NUMBER: P793121

CATALOG NUMBER: LER6D45BD010-EC6DR6540509030-6LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	427.7	9.5
10°-20°	1233.8	27.3
20°-30°	1480.4	32.8
30°-40°	994.8	22.0
40°-50°	297.8	6.6
50°-60°	52.6	1.2
60°-70°	14.9	0.3
70°-80°	7.3	0.2
80°-90°	2.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3141.9	69.6
0°-40°	4136.8	91.7
0°-60°	4487.1	99.5
0°-90°	4511.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4511.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4442	
5°	4429	428
15°	4453	1234
25°	3278	1480
35°	1602	995
45°	331	298
55°	54	53
65°	13	15
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P793121

CATALOG NUMBER: LER6D45BD010-EC6DR6540509030-6LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4442.1
2.5°	4461.1
5°	4428.9
7.5°	4495.8
10°	4532.4
12.5°	4523.5
15°	4452.8
17.5°	4279.9
20°	3988.2
22.5°	3644.8
25°	3277.5
27.5°	2862.7
30°	2397.5
32.5°	1975.8
35°	1602.1
37.5°	1232.8
40°	884.4
42.5°	577.6
45°	331.4
47.5°	175.5
50°	109.2
52.5°	75.8
55°	54.3
57.5°	39.1
60°	27.1
62.5°	17.7
65°	12.6
67.5°	11.4
70°	10.7
72.5°	8.2
75°	6.3
77.5°	5.7
80°	4.4
82.5°	3.2
85°	1.9
87.5°	1.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)