

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793124

Luminaire Tested: LER6D45BD010-EC6DR6540509030-6LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P793124
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D45BD010-EC6DR6540509030-6LBS1H
Description: 6 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4523.1 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 38.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P793124
CATALOG NUMBER: LER6D45BD010-EC6DR6540509030-6LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P793124

CATALOG NUMBER: LER6D45BD010-EC6DR6540509030-6LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72		
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61		
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49		
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	239853
5°	239245
10°	239046
15°	231674
20°	210913
25°	183794
30°	152864
35°	121121
40°	87418
45°	55232
50°	28785
55°	15304
60°	8036
65°	4422
70°	1861
75°	2053
80°	1413
85°	1206

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 55232 cd/sqm



TEST NUMBER: P793124

CATALOG NUMBER: LER6D45BD010-EC6DR6540509030-6LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	388.4	8.6
10°-20°	1063.5	23.5
20°-30°	1300.0	28.7
30°-40°	1054.8	23.3
40°-50°	525.6	11.6
50°-60°	146.6	3.2
60°-70°	33.3	0.7
70°-80°	8.7	0.2
80°-90°	2.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2751.9	60.8
0°-40°	3806.6	84.2
0°-60°	4478.8	99.0
0°-90°	4523.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4523.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4107	
5°	4081	388
15°	3832	1064
25°	2852	1300
35°	1699	1055
45°	669	526
55°	150	147
65°	32	33
75°	9	9
85°	2	2
90°	0	



TEST NUMBER: P793124

CATALOG NUMBER: LER6D45BD010-EC6DR6540509030-6LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	4106.8
2.5°	4103.8
5°	4080.8
7.5°	4067.6
10°	4030.8
12.5°	3955.9
15°	3831.6
17.5°	3637.3
20°	3393.5
22.5°	3130.3
25°	2852.1
27.5°	2554.6
30°	2266.7
32.5°	1982.5
35°	1698.8
37.5°	1415.8
40°	1146.6
42.5°	894.4
45°	668.7
47.5°	465.9
50°	316.8
52.5°	218.5
55°	150.3
57.5°	101.4
60°	68.8
62.5°	47.7
65°	32.0
67.5°	16.3
70°	10.9
72.5°	10.3
75°	9.1
77.5°	6.0
80°	4.2
82.5°	3.0
85°	1.8
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)