

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793591

Luminaire Tested: LER6D50D010-EC6DR6540509027-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793591
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D50D010-EC6DR6540509027-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3648.7 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793591

CATALOG NUMBER: LER6D50D010-EC6DR6540509027-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P793591

CATALOG NUMBER: LER6D50D010-EC6DR6540509027-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	392508
5°	392834
10°	406662
15°	407339
20°	375015
25°	319533
30°	244618
35°	172811
40°	102009
45°	41411
50°	15009
55°	8363
60°	4807
65°	2637
70°	2779
75°	2153
80°	2265
85°	1880

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 41411 cd/sqm



TEST NUMBER: P793591

CATALOG NUMBER: LER6D50D010-EC6DR6540509027-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.9	9.5
10°-20°	997.8	27.3
20°-30°	1197.2	32.8
30°-40°	804.5	22.1
40°-50°	240.8	6.6
50°-60°	42.5	1.2
60°-70°	12.1	0.3
70°-80°	5.9	0.2
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2540.9	69.6
0°-40°	3345.4	91.7
0°-60°	3628.8	99.5
0°-90°	3648.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3648.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3592	
5°	3582	346
15°	3601	998
25°	2650	1197
35°	1296	805
45°	268	241
55°	44	43
65°	10	12
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P793591

CATALOG NUMBER: LER6D50D010-EC6DR6540509027-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3592.4
2.5°	3607.7
5°	3581.7
7.5°	3635.8
10°	3665.4
12.5°	3658.2
15°	3601.1
17.5°	3461.2
20°	3225.3
22.5°	2947.6
25°	2650.5
27.5°	2315.1
30°	1938.9
32.5°	1597.9
35°	1295.6
37.5°	997.0
40°	715.2
42.5°	467.1
45°	268.0
47.5°	141.9
50°	88.3
52.5°	61.3
55°	43.9
57.5°	31.7
60°	22.0
62.5°	14.3
65°	10.2
67.5°	9.2
70°	8.7
72.5°	6.6
75°	5.1
77.5°	4.6
80°	3.6
82.5°	2.6
85°	1.5
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)