

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793600

Luminaire Tested: LER6D50D010-EC6DR6540509030-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P793600
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D50D010-EC6DR6540509030-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5046.3 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793600

CATALOG NUMBER: LER6D50D010-EC6DR6540509030-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P793600

CATALOG NUMBER: LER6D50D010-EC6DR6540509030-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	542851
5°	543301
10°	562431
15°	563358
20°	518670
25°	441934
30°	338320
35°	239009
40°	141089
45°	57280
50°	20755
55°	11563
60°	6643
65°	3645
70°	3833
75°	2997
80°	3083
85°	2633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 57280 cd/sqm



TEST NUMBER: P793600

CATALOG NUMBER: LER6D50D010-EC6DR6540509030-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	478.4	9.5
10°-20°	1380.0	27.3
20°-30°	1655.8	32.8
30°-40°	1112.7	22.1
40°-50°	333.1	6.6
50°-60°	58.8	1.2
60°-70°	16.7	0.3
70°-80°	8.2	0.2
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3514.2	69.6
0°-40°	4626.9	91.7
0°-60°	5018.8	99.5
0°-90°	5046.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5046.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4968	
5°	4954	478
15°	4980	1380
25°	3666	1656
35°	1792	1113
45°	371	333
55°	61	59
65°	14	17
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P793600

CATALOG NUMBER: LER6D50D010-EC6DR6540509030-6LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4968.4
2.5°	4989.6
5°	4953.6
7.5°	5028.4
10°	5069.4
12.5°	5059.5
15°	4980.4
17.5°	4787.0
20°	4460.8
22.5°	4076.7
25°	3665.8
27.5°	3201.9
30°	2681.6
32.5°	2209.9
35°	1791.9
37.5°	1378.9
40°	989.2
42.5°	646.0
45°	370.7
47.5°	196.3
50°	122.1
52.5°	84.7
55°	60.7
57.5°	43.8
60°	30.4
62.5°	19.8
65°	14.1
67.5°	12.7
70°	12.0
72.5°	9.2
75°	7.1
77.5°	6.4
80°	4.9
82.5°	3.5
85°	2.1
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)