

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P793669

Luminaire Tested: LER6D50D010-EC6DR7040509040-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P793669
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D50D010-EC6DR7040509040-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6796.4 lumens
Efficiency: N/A
Efficacy: 144.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P793669

CATALOG NUMBER: LER6D50D010-EC6DR7040509040-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P793669

CATALOG NUMBER: LER6D50D010-EC6DR7040509040-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71			
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65			
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60			
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56			
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51			
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48			
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	586097
5°	584639
10°	583367
15°	583210
20°	577504
25°	542490
30°	483635
35°	385610
40°	256049
45°	153081
50°	79363
55°	41717
60°	14750
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 153081 cd/sqm



TEST NUMBER: P793669

CATALOG NUMBER: LER6D50D010-EC6DR7040509040-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	506.9	7.5
10°-20°	1453.9	21.4
20°-30°	2051.0	30.2
30°-40°	1770.6	26.1
40°-50°	792.9	11.7
50°-60°	207.6	3.1
60°-70°	13.5	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4011.8	59.0
0°-40°	5782.3	85.1
0°-60°	6782.8	99.8
0°-90°	6796.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6796.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5364	
5°	5330	507
15°	5156	1454
25°	4500	2051
35°	2891	1771
45°	991	793
55°	219	208
65°	1	14
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P793669

CATALOG NUMBER: LER6D50D010-EC6DR7040509040-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5364.2
2.5°	5358.5
5°	5330.5
7.5°	5307.3
10°	5258.1
12.5°	5213.8
15°	5155.9
17.5°	5089.3
20°	4966.8
22.5°	4765.2
25°	4499.9
27.5°	4192.2
30°	3833.4
32.5°	3394.5
35°	2891.0
37.5°	2335.3
40°	1795.2
42.5°	1364.0
45°	990.7
47.5°	683.0
50°	466.9
52.5°	322.2
55°	219.0
57.5°	132.2
60°	67.5
62.5°	21.2
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)