

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794558

Luminaire Tested: LER6D60D010-EC6DR6555659027-6LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P794558
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR6555659027-6LBS1MW
Description: 6 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6091.2 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P794558

CATALOG NUMBER: LER6D60D010-EC6DR6555659027-6LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P794558

CATALOG NUMBER: LER6D60D010-EC6DR6555659027-6LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	323014
5°	322196
10°	321924
15°	312001
20°	284035
25°	247520
30°	205864
35°	163123
40°	117731
45°	74377
50°	38770
55°	20609
60°	10828
65°	5956
70°	2493
75°	2753
80°	1917
85°	1608

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 74377 cd/sqm



TEST NUMBER: P794558

CATALOG NUMBER: LER6D60D010-EC6DR6555659027-6LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	523.0	8.6
10°-20°	1432.3	23.5
20°-30°	1750.7	28.7
30°-40°	1420.5	23.3
40°-50°	707.8	11.6
50°-60°	197.4	3.2
60°-70°	44.9	0.7
70°-80°	11.7	0.2
80°-90°	3.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3706.0	60.8
0°-40°	5126.4	84.2
0°-60°	6031.7	99.0
0°-90°	6091.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6091.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5531	
5°	5496	523
15°	5160	1432
25°	3841	1751
35°	2288	1420
45°	900	708
55°	202	197
65°	43	45
75°	12	12
85°	2	3
90°	0	



TEST NUMBER: P794558

CATALOG NUMBER: LER6D60D010-EC6DR6555659027-6LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5530.7
2.5°	5526.6
5°	5495.7
7.5°	5477.8
10°	5428.3
12.5°	5327.5
15°	5160.1
17.5°	4898.4
20°	4570.0
22.5°	4215.7
25°	3841.0
27.5°	3440.3
30°	3052.6
32.5°	2669.8
35°	2287.9
37.5°	1906.7
40°	1544.2
42.5°	1204.5
45°	900.5
47.5°	627.4
50°	426.7
52.5°	294.2
55°	202.4
57.5°	136.5
60°	92.7
62.5°	64.2
65°	43.1
67.5°	21.9
70°	14.6
72.5°	13.8
75°	12.2
77.5°	8.1
80°	5.7
82.5°	4.1
85°	2.4
87.5°	1.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)