

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P794584

Luminaire Tested: LER6D60D010-EC6DR6555659050-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P794584
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D60D010-EC6DR6555659050-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6683.7 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P794584

CATALOG NUMBER: LER6D60D010-EC6DR6555659050-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P794584

CATALOG NUMBER: LER6D60D010-EC6DR6555659050-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	719001
5°	719598
10°	744927
15°	746163
20°	686963
25°	585335
30°	448095
35°	316571
40°	186859
45°	75853
50°	27503
55°	15315
60°	8785
65°	4835
70°	5079
75°	3968
80°	4090
85°	3510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 75853 cd/sqm



TEST NUMBER: P794584

CATALOG NUMBER: LER6D60D010-EC6DR6555659050-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	633.7	9.5
10°-20°	1827.8	27.3
20°-30°	2193.0	32.8
30°-40°	1473.8	22.1
40°-50°	441.2	6.6
50°-60°	77.9	1.2
60°-70°	22.1	0.3
70°-80°	10.9	0.2
80°-90°	3.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4654.5	69.6
0°-40°	6128.3	91.7
0°-60°	6647.3	99.5
0°-90°	6683.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6683.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6581	
5°	6561	634
15°	6596	1828
25°	4855	2193
35°	2373	1474
45°	491	441
55°	80	78
65°	19	22
75°	9	11
85°	3	3
90°	0	



TEST NUMBER: P794584

CATALOG NUMBER: LER6D60D010-EC6DR6555659050-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	6580.6
2.5°	6608.6
5°	6561.0
7.5°	6660.1
10°	6714.3
12.5°	6701.2
15°	6596.5
17.5°	6340.3
20°	5908.2
22.5°	5399.5
25°	4855.3
27.5°	4240.9
30°	3551.7
32.5°	2927.0
35°	2373.4
37.5°	1826.3
40°	1310.1
42.5°	855.7
45°	490.9
47.5°	260.0
50°	161.8
52.5°	112.2
55°	80.4
57.5°	58.0
60°	40.2
62.5°	26.2
65°	18.7
67.5°	16.8
70°	15.9
72.5°	12.2
75°	9.4
77.5°	8.4
80°	6.5
82.5°	4.7
85°	2.8
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)