

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P845517

Luminaire Tested: SQ2R-FB-050D-830-UNV-STD-W-4

Issue Date: 6/14/2024

Test Information

Test Method: LM-79-2019
Report Number: P845517
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-12)
Test Lab: INNOVATION CENTER
Issue Date: 6/14/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ2R-FB-050D-830-UNV-STD-W-4
Description: CONTINUA SQ2 RECESSED, BATWING LENS
500 LUMENS PER FOOT
Light Source: 3000K CCT, 80 CRI LEDS
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2328.8 lumens
Efficiency: N/A
Efficacy: 130.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 2.99 / 2.56
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 17.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9973
Total Harmonic Distortion (THDi): 0.0531
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P845517
CATALOG NUMBER: SQ2R-FB-050D-830-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P845517

CATALOG NUMBER: SQ2R-FB-050D-830-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84
2	98	90	83	77	96	88	82	76	84	79	74	81	77	73	78	74	71	69
3	89	78	70	63	87	77	69	63	74	67	62	71	65	60	68	64	59	57
4	81	69	60	53	79	67	59	52	65	58	52	63	56	51	60	55	50	48
5	74	61	52	45	72	60	51	45	58	50	44	56	49	44	54	48	43	41
6	68	54	45	39	66	53	45	38	52	44	38	50	43	38	48	42	37	35
7	63	49	40	34	61	48	40	33	47	39	33	45	38	33	44	37	33	31
8	58	44	36	30	57	44	35	29	42	35	29	41	34	29	40	34	29	27
9	54	40	32	26	53	40	32	26	39	31	26	38	31	26	37	30	26	24
10	51	37	29	23	49	37	29	23	36	28	23	35	28	23	34	28	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3798	3798	3798
5°	3702	5131	6724
10°	3466	9935	13086
15°	3137	12928	15062
20°	2778	14220	15775
25°	2457	15207	16033
30°	2172	15662	16231
35°	1940	15934	17450
40°	1764	16086	18539
45°	1626	16162	19413
50°	1535	16473	19766
55°	1495	16901	19924
60°	1534	17124	19824
65°	1597	16890	19266
70°	1652	16334	14573
75°	1834	14672	8041
80°	1897	7569	7466
85°	1890	5243	3149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 55°
 Luminance: 19924 cd/sqm



TEST NUMBER: P845517

CATALOG NUMBER: SQ2R-FB-050D-830-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.7	1.7
10°-20°	180.5	7.8
20°-30°	317.8	13.6
30°-40°	411.0	17.6
40°-50°	453.3	19.5
50°-60°	422.8	18.2
60°-70°	327.2	14.1
70°-80°	149.6	6.4
80°-90°	28.0	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	537.0	23.1
0°-40°	948.0	40.7
0°-60°	1824.1	78.3
0°-90°	2328.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2328.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	235	235	235	235	235	
5°	228	262	317	386	415	21
15°	188	374	773	865	901	52
25°	138	505	854	891	900	63
35°	98	488	808	836	885	62
45°	71	374	708	812	850	55
55°	53	223	600	690	708	48
65°	42	126	442	495	504	41
75°	29	77	235	127	129	30
85°	10	23	28	19	17	11
90°	0	0	0	0	0	



TEST NUMBER: P845517

CATALOG NUMBER: SQ2R-FB-050D-830-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	235.2	235.2	235.2	235.2	235.2
2.5°	232.9	245.3	258.9	274.7	281.5
5°	228.4	262.3	316.6	385.5	414.9
7.5°	221.6	283.8	424.0	615.1	680.6
10°	211.4	307.5	606.0	766.6	798.2
12.5°	200.1	339.2	720.2	820.8	853.6
15°	187.7	374.2	773.4	864.9	901.1
17.5°	175.2	412.7	803.9	897.7	919.2
20°	161.7	453.4	827.6	905.6	918.1
22.5°	149.2	483.9	844.6	898.9	912.4
25°	137.9	505.4	853.6	890.9	900.0
27.5°	126.6	513.3	850.2	876.2	884.2
30°	116.5	511.0	840.1	858.2	870.6
32.5°	107.4	504.3	825.4	842.3	872.9
35°	98.4	488.4	808.4	835.5	885.3
37.5°	90.5	465.8	786.9	838.9	888.7
40°	83.7	439.8	763.2	838.9	879.6
42.5°	76.9	409.3	736.0	827.6	868.3
45°	71.2	374.2	707.8	811.8	850.2
47.5°	65.6	335.8	681.8	792.6	822.0
50°	61.1	296.2	655.8	764.3	786.9
52.5°	56.5	257.8	629.8	730.4	750.7
55°	53.1	222.7	600.4	689.7	707.8
57.5°	49.7	191.1	568.7	646.7	661.4
60°	47.5	166.2	530.3	599.2	613.9
62.5°	44.1	143.6	487.3	549.5	563.1
65°	41.8	125.5	442.1	495.2	504.3
67.5°	38.4	110.8	394.6	433.0	424.0
70°	35.0	100.6	346.0	357.3	308.7
72.5°	32.8	89.3	292.8	258.9	156.0
75°	29.4	76.9	235.2	126.6	128.9
77.5°	24.9	62.2	173.0	101.8	104.0
80°	20.4	48.6	81.4	79.1	80.3
82.5°	15.8	35.0	49.7	53.1	50.9
85°	10.2	22.6	28.3	19.2	17.0
87.5°	4.5	10.2	5.7	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P845517

CATALOG NUMBER: SQ2R-FB-050D-830-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.53	17.22	15.90	17.53	17.84	24.19	25.87	24.55	26.18	26.50
	3H	16.32	17.84	16.70	18.17	18.53	25.87	27.39	26.25	27.72	28.08
	4H	16.65	18.09	17.05	18.44	18.81	26.09	27.52	26.49	27.87	28.24
	6H	16.91	18.24	17.32	18.60	18.99	26.22	27.55	26.63	27.91	28.30
	8H	16.99	18.26	17.41	18.65	19.05	26.24	27.51	26.67	27.90	28.30
	12H	17.05	18.26	17.47	18.64	19.07	26.24	27.46	26.67	27.84	28.27
4H	2H	19.97	21.40	20.36	21.75	22.12	24.72	26.16	25.12	26.51	26.88
	3H	20.98	22.18	21.39	22.58	22.98	26.63	27.83	27.04	28.23	28.63
	4H	21.30	22.39	21.73	22.80	23.23	26.90	27.99	27.33	28.40	28.84
	6H	21.49	22.43	21.94	22.87	23.32	27.10	28.04	27.55	28.48	28.94
	8H	21.53	22.41	21.99	22.85	23.32	27.14	28.03	27.60	28.47	28.93
	12H	21.56	22.35	22.04	22.83	23.30	27.16	27.95	27.64	28.43	28.89
8H	4H	22.54	23.42	23.00	23.87	24.33	27.09	27.98	27.55	28.42	28.88
	6H	22.82	23.55	23.31	24.04	24.51	27.34	28.07	27.83	28.55	29.03
	8H	22.90	23.56	23.41	24.06	24.55	27.41	28.06	27.92	28.57	29.05
	12H	22.97	23.55	23.47	24.04	24.60	27.44	28.02	27.95	28.51	29.07
12H	4H	22.60	23.39	23.08	23.87	24.33	27.08	27.88	27.56	28.35	28.82
	6H	22.92	23.58	23.43	24.08	24.57	27.33	27.98	27.84	28.49	28.97
	8H	23.07	23.64	23.57	24.13	24.69	27.44	28.01	27.94	28.50	29.06