

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P845500

Luminaire Tested: SQ2R-FA-075D-835-UNV-STD-W-4

Issue Date: 6/14/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P845500  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2308-131-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 6/14/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ2R-FA-075D-835-UNV-STD-W-4  
Description: CONTINUA SQ2 RECESSED, ASYMMETRIC LENS  
750 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3158.2 lumens  
Efficiency: N/A  
Efficacy: 118.3 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 0.95 / 0.93  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 26.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P845500  
CATALOG NUMBER: SQ2R-FA-075D-835-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P845500

CATALOG NUMBER: SQ2R-FA-075D-835-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88				88
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78				78
3	96	88	81	76	94	86	80	75	84	78	74	81	77	73	79	75	72	70				70
4	90	80	73	68	88	79	72	67	77	71	66	75	70	66	73	68	65	63				63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57				57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52				52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48				48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	55	49	46	44				44
9	66	55	48	43	65	54	47	43	53	47	43	52	46	42	51	46	42	41				41
10	63	51	44	40	61	51	44	40	50	44	40	49	43	39	48	43	39	38				38

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	34951	34951	34951	34951
5°	34767	34820	34635	34794
10°	34715	34580	34580	34580
15°	34601	34247	34328	34247
20°	34333	32874	34081	33184
25°	33882	27745	33649	28328
30°	33572	15918	33206	16130
35°	32981	13675	32564	13482
40°	32068	7191	31175	7122
45°	29149	3094	28106	3094
50°	19231	3733	18249	3486
55°	10753	6894	10201	6249
60°	5800	9700	5693	8699
65°	5116	11786	5364	13410
70°	4777	14106	4546	14875
75°	4479	12121	4585	12526
80°	3794	8656	3794	9112
85°	3335	4835	3020	5743

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29149 cd/sqm



TEST NUMBER: P845500

CATALOG NUMBER: SQ2R-FA-075D-835-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	203.9	6.5
10°-20°	578.5	18.3
20°-30°	791.3	25.1
30°-40°	662.7	21.0
40°-50°	371.5	11.8
50°-60°	197.0	6.2
60°-70°	183.7	5.8
70°-80°	135.1	4.3
80°-90°	34.6	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1573.7	49.8
0°-40°	2236.4	70.8
0°-60°	2804.9	88.8
0°-90°	3158.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3158.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2165	2165	2165	2165	2165	
5°	2145	2148	2137	2147	2145	204
15°	2070	2049	2054	2049	2070	584
25°	1902	1557	1889	1590	1902	877
35°	1673	694	1652	684	1673	1046
45°	1277	136	1231	136	1277	942
55°	382	245	362	222	382	361
65°	134	308	140	351	134	134
75°	72	194	74	201	72	74
85°	18	26	16	31	18	21
90°	0	0	0	0	0	



TEST NUMBER: P845500

CATALOG NUMBER: SQ2R-FA-075D-835-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	2164.7	2164.7	2164.7	2164.7	2164.7	2164.7	2164.7	2164.7	2164.7	2164.7	2164.7
2.5°	2150.0	2190.8	2154.9	2150.0	2164.7	2161.4	2156.6	2176.1	2143.5	2176.1	2150.0
5°	2145.1	2182.7	2140.2	2128.8	2148.4	2135.3	2146.8	2169.6	2137.0	2166.3	2133.7
7.5°	2135.3	2169.6	2119.0	2110.8	2130.4	2119.0	2123.9	2154.9	2127.2	2146.8	2117.4
10°	2117.4	2146.8	2096.1	2091.3	2109.2	2097.8	2102.7	2135.3	2109.2	2127.2	2097.8
12.5°	2097.8	2119.0	2068.4	2066.8	2081.5	2074.9	2076.6	2102.7	2083.1	2101.0	2073.3
15°	2070.0	2091.3	2040.6	2032.5	2048.8	2042.3	2045.5	2070.0	2053.7	2065.1	2040.6
17.5°	2039.0	2055.3	2006.4	1988.4	1990.0	1998.2	2006.4	2035.7	2019.4	2034.1	2003.1
20°	1998.2	2017.8	1962.3	1916.6	1913.3	1921.5	1962.3	1991.7	1983.5	1999.8	1950.9
22.5°	1950.9	1962.3	1913.3	1828.4	1815.4	1823.5	1906.8	1942.7	1941.1	1950.9	1887.2
25°	1901.9	1914.9	1823.5	1715.8	1557.4	1706.0	1826.8	1888.8	1888.8	1898.6	1818.6
27.5°	1852.9	1856.2	1725.6	1155.8	999.1	1108.5	1722.3	1823.5	1836.6	1834.9	1717.4
30°	1800.7	1789.2	1487.2	889.7	853.8	876.7	1488.9	1755.0	1781.1	1763.1	1449.7
32.5°	1740.3	1702.7	1000.7	799.9	772.2	791.8	955.0	1673.3	1723.9	1679.9	1062.8
35°	1673.3	1588.4	837.5	723.2	693.8	719.9	830.9	1560.7	1652.1	1547.6	865.2
37.5°	1604.8	1325.6	755.9	615.5	556.7	605.7	752.6	1320.7	1572.1	1265.2	759.1
40°	1521.5	981.1	662.8	422.8	341.2	398.3	657.9	935.4	1479.1	1008.9	646.5
42.5°	1410.5	829.3	499.5	230.2	176.3	207.3	473.4	816.3	1364.8	837.5	481.6
45°	1276.6	737.9	315.1	146.9	135.5	142.0	290.6	724.8	1230.9	708.5	321.6
47.5°	1072.6	592.6	213.9	124.1	133.9	124.1	207.3	574.6	1012.2	563.2	213.9
50°	765.6	439.1	156.7	125.7	148.6	125.7	151.8	424.5	726.5	465.3	155.1
52.5°	517.5	351.0	120.8	140.4	186.1	143.7	117.5	342.8	491.4	354.3	112.6
55°	382.0	290.6	102.8	181.2	244.9	186.1	102.8	282.4	362.4	279.2	99.6
57.5°	257.9	228.6	101.2	230.2	274.3	235.1	102.8	220.4	246.5	222.0	89.8
60°	179.6	171.4	115.9	248.1	300.4	251.4	117.5	164.9	176.3	163.3	98.0
62.5°	140.4	125.7	145.3	274.3	315.1	264.5	148.6	119.2	148.6	112.6	111.0
65°	133.9	86.5	164.9	272.6	308.5	272.6	166.5	81.6	140.4	88.2	146.9
67.5°	125.7	65.3	161.6	269.4	313.4	272.6	156.7	62.0	120.8	60.4	143.7
70°	101.2	57.1	150.2	275.9	298.8	266.1	150.2	55.5	96.3	53.9	176.3
72.5°	80.0	53.9	137.1	249.8	256.3	240.0	138.8	53.9	81.6	47.3	163.3
75°	71.8	53.9	133.9	204.1	194.3	194.3	130.6	52.2	73.5	49.0	129.0
77.5°	57.1	49.0	115.9	142.0	133.9	133.9	114.3	47.3	53.9	44.1	109.4
80°	40.8	44.1	91.4	98.0	93.1	93.1	88.2	42.4	40.8	40.8	86.5
82.5°	29.4	35.9	65.3	65.3	62.0	60.4	63.7	35.9	29.4	32.7	62.0
85°	18.0	26.1	37.5	31.0	26.1	24.5	35.9	24.5	16.3	24.5	35.9
87.5°	8.2	14.7	6.5	6.5	6.5	6.5	6.5	14.7	8.2	13.1	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P845500

CATALOG NUMBER: SQ2R-FA-075D-835-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	247.5°	270°	292.5°	315°	337.5°	360°
0°	2164.7	2164.7	2164.7	2164.7	2164.7	2164.7
2.5°	2143.5	2154.9	2154.9	2148.4	2181.0	2150.0
5°	2125.5	2146.8	2137.0	2137.0	2169.6	2145.1
7.5°	2114.1	2135.3	2125.5	2122.3	2154.9	2135.3
10°	2094.5	2109.2	2102.7	2107.6	2137.0	2117.4
12.5°	2066.8	2084.7	2078.2	2086.4	2112.5	2097.8
15°	2034.1	2048.8	2052.1	2055.3	2086.4	2070.0
17.5°	1983.5	1990.0	2008.0	2025.9	2057.0	2039.0
20°	1921.5	1931.3	1941.1	1980.2	2017.8	1998.2
22.5°	1851.3	1844.7	1870.9	1918.2	1967.2	1950.9
25°	1715.8	1590.1	1728.8	1844.7	1906.8	1901.9
27.5°	1260.3	1077.5	1237.4	1748.4	1846.4	1852.9
30°	940.3	865.2	938.7	1519.9	1777.8	1800.7
32.5°	808.1	762.4	799.9	1066.0	1691.3	1740.3
35°	719.9	684.0	719.9	865.2	1572.1	1673.3
37.5°	613.8	545.3	615.5	767.3	1330.5	1604.8
40°	431.0	337.9	417.9	669.3	1005.6	1521.5
42.5°	251.4	187.7	235.1	491.4	832.6	1410.5
45°	155.1	135.5	148.6	318.3	705.2	1276.6
47.5°	122.4	125.7	122.4	212.2	561.6	1072.6
50°	115.9	138.8	115.9	155.1	447.3	765.6
52.5°	129.0	153.5	127.3	114.3	346.1	517.5
55°	142.0	222.0	143.7	99.6	269.4	382.0
57.5°	202.4	244.9	205.7	93.1	220.4	257.9
60°	209.0	269.4	207.3	99.6	161.6	179.6
62.5°	256.3	349.4	256.3	117.5	109.4	140.4
65°	318.3	351.0	321.6	145.3	84.9	133.9
67.5°	303.6	328.1	300.4	150.2	58.8	125.7
70°	297.1	315.1	293.9	177.9	53.9	101.2
72.5°	272.6	271.0	266.1	161.6	47.3	80.0
75°	215.5	200.8	207.3	142.0	49.0	71.8
77.5°	142.0	135.5	137.1	112.6	44.1	57.1
80°	101.2	98.0	96.3	91.4	40.8	40.8
82.5°	68.6	65.3	63.7	65.3	32.7	29.4
85°	34.3	31.0	29.4	40.8	24.5	18.0
87.5°	8.2	8.2	6.5	8.2	11.4	8.2
90°	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P845500

CATALOG NUMBER: SQ2R-FA-075D-835-UNV-STD-W-4

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.33	17.64	16.70	17.95	18.27	15.17	16.48	15.54	16.79	17.11
	3H	17.05	18.22	17.43	18.55	18.92	21.38	22.55	21.76	22.88	23.24
	4H	17.48	18.57	17.88	18.92	19.31	22.67	23.77	23.08	24.12	24.50
	6H	17.85	18.86	18.27	19.23	19.63	23.30	24.31	23.71	24.68	25.07
	8H	17.98	18.94	18.41	19.33	19.74	23.43	24.39	23.86	24.78	25.19
	12H	18.07	18.98	18.50	19.37	19.80	23.49	24.40	23.92	24.79	25.22
4H	2H	16.77	17.87	17.17	18.22	18.60	15.76	16.85	16.16	17.20	17.58
	3H	17.79	18.70	18.20	19.10	19.51	22.13	23.04	22.54	23.44	23.84
	4H	18.36	19.18	18.80	19.60	20.04	23.59	24.41	24.03	24.83	25.27
	6H	18.86	19.57	19.32	20.01	20.48	24.35	25.06	24.81	25.51	25.97
	8H	19.04	19.70	19.50	20.15	20.62	24.52	25.19	24.99	25.63	26.10
	12H	19.17	19.76	19.66	20.24	20.72	24.60	25.19	25.09	25.67	26.15
8H	4H	19.49	20.16	19.96	20.60	21.07	23.74	24.40	24.21	24.85	25.32
	6H	20.11	20.66	20.62	21.15	21.63	24.63	25.18	25.13	25.67	26.15
	8H	20.35	20.84	20.87	21.35	21.84	24.88	25.37	25.40	25.88	26.37
	12H	20.55	20.97	21.06	21.47	22.04	25.02	25.45	25.54	25.94	26.51
12H	4H	19.66	20.25	20.14	20.73	21.20	23.72	24.31	24.21	24.79	25.26
	6H	20.39	20.87	20.91	21.39	21.88	24.64	25.13	25.16	25.64	26.13
	8H	20.71	21.14	21.23	21.63	22.20	24.94	25.37	25.46	25.86	26.43